



# FDMS4435BZ

## P-Channel PowerTrench<sup>®</sup> MOSFET -30 V, -18 A, 20 mΩ

### Features

- Max  $r_{DS(on)}$  = 20 mΩ at  $V_{GS} = -10$  V,  $I_D = -9.0$  A
- Max  $r_{DS(on)}$  = 37 mΩ at  $V_{GS} = -4.5$  V,  $I_D = -6.5$  A
- Extended  $V_{GSS}$  range (-25 V) for battery applications
- High performance trench technology for extremely low  $r_{DS(on)}$
- High power and current handling capability
- HBM ESD protection level >7 kV typical (Note 4)
- 100% UIL tested
- Termination is Lead-free and RoHS Compliant




### General Description


This P-Channel MOSFET is produced using Fairchild Semiconductor's advanced Power Trench<sup>®</sup> process that has been especially tailored to minimize the on-state resistance. This device is well suited for Power Management and load switching applications common in Notebook Computers and Portable Battery Packs.

### Applications

- High side in DC-DC Buck Converters
- Notebook battery power management
- Load switch in Notebook



Power 56



### MOSFET Maximum Ratings $T_A = 25$ °C unless otherwise noted

| Symbol         | Parameter   | Rated       | Units |
|----------------|---|-------------|-------|
| $V_{DS}$       | Drain to Source Voltage                                   | -30         | V     |
| $V_{GS}$       | Gate to Source Voltage                                    | ±25         | V     |
| $I_D$          | Drain Current -Continuous (Package limited) $T_C = 25$ °C | -18         | A     |
|                | -Continuous (Silicon limited) $T_C = 25$ °C               | -35         |       |
|                | -Continuous $T_A = 25$ °C (Note 1a)                       | -9.0        |       |
|                | -Pulsed   | -50         |       |
| $E_{AS}$       | Single Pulse Avalanche Energy (Note 3)                    | 18          | mJ    |
| $P_D$          | Power Dissipation $T_C = 25$ °C                           | 39          | W     |
|                | Power Dissipation $T_A = 25$ °C (Note 1a)                 | 2.5         |       |
| $T_J, T_{STG}$ | Operating and Storage Junction Temperature Range          | -55 to +150 | °C    |

### Thermal Characteristics

|                 |   |     |      |
|-----------------|---|-----|------|
| $R_{\theta JC}$ | Thermal Resistance, Junction to Case              | 3.2 | °C/W |
| $R_{\theta JA}$ | Thermal Resistance, Junction to Ambient (Note 1a) | 50  |      |

### Package Marking and Ordering Information

| Device Marking | Device     | Package  | Reel Size | Tape Width | Quantity   |
|----------------|------------|----------|-----------|------------|------------|
| FDMS4435BZ     | FDMS4435BZ | Power 56 | 13 "      | 12 mm      | 3000 units |

## Electrical Characteristics $T_J = 25\text{ }^\circ\text{C}$ unless otherwise noted

| Symbol                               | Parameter                                 | Test Conditions  | Min | Typ | Max      | Units                |
|--------------------------------------|---|--|-----|-----|----------|----------------------|
| $BV_{DSS}$                           | Drain to Source Breakdown Voltage         | $I_D = -250\ \mu\text{A}, V_{GS} = 0\ \text{V}$                      | -30 |     |          | V                    |
| $\frac{\Delta BV_{DSS}}{\Delta T_J}$ | Breakdown Voltage Temperature Coefficient | $I_D = -250\ \mu\text{A}$ , referenced to $25\text{ }^\circ\text{C}$ |     | -23 |          | mV/ $^\circ\text{C}$ |
| $I_{DSS}$                            | Zero Gate Voltage Drain Current           | $V_{DS} = -24\ \text{V}, V_{GS} = 0\ \text{V}$                       |     |     | -1       | $\mu\text{A}$        |
| $I_{GSS}$                            | Gate to Source Leakage Current            | $V_{GS} = \pm 25\ \text{V}, V_{DS} = 0\ \text{V}$                    |     |     | $\pm 10$ | $\mu\text{A}$        |

## On Characteristics

|  |  |   |      |      |      |                      |
|--|--|---|------|------|------|----------------------|
| $V_{GS(th)}$                           | Gate to Source Threshold Voltage                         | $V_{GS} = V_{DS}, I_D = -250\ \mu\text{A}$  | -1.0 | -1.9 | -3.0 | V                    |
| $\frac{\Delta V_{GS(th)}}{\Delta T_J}$ | Gate to Source Threshold Voltage Temperature Coefficient | $I_D = -250\ \mu\text{A}$ , referenced to $25\text{ }^\circ\text{C}$                |      | 6    |      | mV/ $^\circ\text{C}$ |
| $r_{DS(on)}$                           | Static Drain to Source On Resistance                     | $V_{GS} = -10\ \text{V}, I_D = -9.0\ \text{A}$                                      |      | 15   | 20   | m $\Omega$           |
|  |  | $V_{GS} = -4.5\ \text{V}, I_D = -6.5\ \text{A}$                                     |      | 22   | 37   |                      |
|  |  | $V_{GS} = -10\ \text{V}, I_D = -9.0\ \text{A}$<br>$T_J = 125\text{ }^\circ\text{C}$ |      | 21   | 28   |                      |
| $g_{FS}$                               | Forward Transconductance                                 | $V_{DS} = -5\ \text{V}, I_D = -9.0\ \text{A}$                                       |      | 25   |      | S                    |

## Dynamic Characteristics

|           |                              |  |  |      |      |          |
|-----------|------------------------------|--|--|------|------|----------|
| $C_{iss}$ | Input Capacitance            | $V_{DS} = -15\ \text{V}, V_{GS} = 0\ \text{V},$<br>$f = 1\ \text{MHz}$ |  | 1540 | 2050 | pF       |
| $C_{oss}$ | Output Capacitance           |  |  | 290  | 390  | pF       |
| $C_{rSS}$ | Reverse Transfer Capacitance |  |  | 260  | 385  | pF       |
| $R_g$     | Gate Resistance              |  |  | 5    |      | $\Omega$ |

## Switching Characteristics


|              |                               |  |   |   |    |    |    |
|--------------|-------------------------------|--|---|---|----|----|----|
| $t_{d(on)}$  | Turn-On Delay Time            | $V_{DD} = -15\ \text{V}, I_D = -9.0\ \text{A},$<br>$V_{GS} = -10\ \text{V}, R_{GEN} = 6\ \Omega$ |   | 9   | 17 | ns |    |
| $t_r$        | Rise Time                     |  |   | 10  | 18 | ns |    |
| $t_{d(off)}$ | Turn-Off Delay Time           |  |   | 35  | 56 | ns |    |
| $t_f$        | Fall Time                     |  |   | 19  | 33 | ns |    |
| $Q_g$        | Total Gate Charge             |  | $V_{GS} = 0\ \text{V to } -10\ \text{V}$  |   | 34 | 47 | nC |
| $Q_g$        | Total Gate Charge             |  | $V_{GS} = 0\ \text{V to } -4.5\ \text{V}$ | $V_{DD} = -15\ \text{V},$<br>$I_D = -9.0\ \text{A}$ | 18 | 25 | nC |
| $Q_{gs}$     | Gate to Source Charge         |  |   | 5   |    | nC |    |
| $Q_{gd}$     | Gate to Drain "Miller" Charge |  |   | 9   |    | nC |    |

## Drain-Source Diode Characteristics

|          |                                       |   |  |      |     |    |
|----------|---------------------------------------|---|--|------|-----|----|
| $V_{SD}$ | Source to Drain Diode Forward Voltage | $V_{GS} = 0\ \text{V}, I_S = -1.9\ \text{A}$ (Note 2)     |  | 0.75 | 1.2 | V  |
|          |                                       | $V_{GS} = 0\ \text{V}, I_S = -9.0\ \text{A}$ (Note 2)     |  | 0.86 | 1.5 |    |
| $t_{rr}$ | Reverse Recovery Time                 | $I_F = -9.0\ \text{A}, di/dt = 100\ \text{A}/\mu\text{s}$ |  | 25   | 39  | ns |
| $Q_{rr}$ | Reverse Recovery Charge               |   |  | 12   | 21  | nC |

Notes:

- $R_{\theta JA}$  is determined with the device mounted on a 1 in<sup>2</sup> pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material.  $R_{\theta JC}$  is guaranteed by design while  $R_{\theta CA}$  is determined by the user's board design.



a) 50  $^\circ\text{C}/\text{W}$  when mounted on a 1 in<sup>2</sup> pad of 2 oz copper




b) 125  $^\circ\text{C}/\text{W}$  when mounted on a minimum pad of 2 oz copper.

2. Pulse Test: Pulse Width < 300  $\mu\text{s}$ , Duty cycle < 2.0%.


3.  $E_{AS}$  of 18 mJ is based on starting  $T_J = 25\text{ }^\circ\text{C}$ ,  $L = 1\ \text{mH}$ ,  $I_{AS} = -6\ \text{A}$ ,  $V_{DD} = -27\ \text{V}$ ,  $V_{GS} = -10\ \text{V}$ . 100% tested at  $L = 0.3\ \text{mH}$ ,  $I_{AS} = -8\ \text{A}$ .

4. The diode connected between the gate and source serves only as protection against ESD. No gate overvoltage rating is implied.


**Typical Characteristics**  $T_J = 25\text{ }^\circ\text{C}$  unless otherwise noted




**Figure 1. On-Region Characteristics**




**Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage**




**Figure 3. Normalized On-Resistance vs Junction Temperature**



**Figure 4. On-Resistance vs Gate to Source Voltage**




**Figure 5. Transfer Characteristics**




**Figure 6. Source to Drain Diode Forward Voltage vs Source Current**


**Typical Characteristics**  $T_J = 25\text{ }^\circ\text{C}$  unless otherwise noted




**Figure 7. Gate Charge Characteristics**




**Figure 8. Capacitance vs Drain to Source Voltage**




**Figure 9. Unclamped Inductive Switching Capability**



**Figure 10. Maximum Continuous Drain Current vs Case Temperature**




**Figure 11. Gate Leakage Current vs Gate to Source Voltage**




**Figure 12. Forward Bias Safe Operating Area**

**Typical Characteristics**  $T_J = 25\text{ }^\circ\text{C}$  unless otherwise noted




**Figure 13. Single Pulse Maximum Power Dissipation**



**Figure 14. Junction-to-Ambient Transient Thermal Response Curve**

## Dimensional Outline and Pad Layout







Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:  
[https://www.fairchildsemi.com/evaluate/package-specifications/packageDetails.html?id=PN\\_PQOAM-008](https://www.fairchildsemi.com/evaluate/package-specifications/packageDetails.html?id=PN_PQOAM-008)



**TRADEMARKS**

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

- |   |   |   |   |
|---|---|---|---|
| AccuPower™  | F-PFST™   |  | SYSTEM GENERAL®   |
| Awinda®   | FRFET®  | PowerTrench®  | TinyBoost®  |
| AX-CAP®*  | Global Power ResourceSM                         | PowerXS™  | TinyBuck™   |
| BitSiC™   | GreenBridge™                                    | Programmable Active Droop™  | TinyCalc™   |
| Build it Now™   | Green FPS™                                      | QFET®   | TinyLogic®  |
| CorePLUS™   | Green FPS™ e-Series™                            | QS™   | TINYOPTO™   |
| CorePOWER™  | Gmax™   | Quiet Series™   | TinyPower™  |
| CROSSVOLT™  | GTO™  | RapidConfigure™   | TinyPWM™  |
| CTL™  | IntelliMAX™                                     |  | TinyWire™   |
| Current Transfer Logic™   | ISOPLANAR™                                      | Saving our world, 1mW/W/kW at a time™   | TranSiC™  |
| DEUXPEED®   | Marking Small Speakers Sound Louder and Better™ | SignalWise™   | TriFault Detect™  |
| Dual Cool™  | MegaBuck™                                       | SmartMax™   | TRUECURRENT®*   |
| EcoSPARK®   | MICROCOUPLER™                                   | SMART START™  | μSerDes™  |
| EfficientMax™   | MicroFET™                                       | Solutions for Your Success™   |  |
| ESBC™   | MicroPak™                                       | SPM®  | UHC®  |
|  | MicroPak2™                                      | STEALTH™  | Ultra FRFET™  |
| Fairchild®  | MillerDrive™                                    | SuperFET®   | UniFET™   |
| Fairchild Semiconductor®  | MotionMax™                                      | SuperSOT™-3   | VCX™  |
| FACT Quiet Series™  | MotionGrid®                                     | SuperSOT™-6   | VisualMax™  |
| FACT®   | MTi®  | SuperSOT™-8   | VoltagePlus™  |
| FAST®   | MTx®  | SupreMOS®   | XST™  |
| FastvCore™  | MVN®  | SyncFET™  | Xsens™  |
| FETBench™   | mWSaver®  | Sync-Lock™  | 仙童™   |
| FPS™  | OptoHiT™  |   |   |

\*Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

**DISCLAIMER**

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. TO OBTAIN THE LATEST, MOST UP-TO-DATE DATASHEET AND PRODUCT INFORMATION, VISIT OUR WEBSITE AT [HTTP://WWW.FAIRCHILDSEMI.COM](http://www.fairchildsemi.com). FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

**LIFE SUPPORT POLICY**

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used here in:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**ANTI-COUNTERFEITING POLICY**

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, [www.fairchildsemi.com](http://www.fairchildsemi.com), under Sales Support.


Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

**PRODUCT STATUS DEFINITIONS**



**Definition of Terms**

| Datasheet Identification | Product Status        | Definition  |
|--------------------------|-----------------------|---|
| Advance Information      | Formative / In Design | Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.   |
| Preliminary              | First Production      | Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. |
| No Identification Needed | Full Production       | Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.   |
| Obsolete                 | Not In Production     | Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.  |


Rev. I71



TOP VIEW




LAND PATTERN RECOMMENDATION




SIDE VIEW

OPTIONAL DRAFT ANGLE MAY APPEAR ON FOUR SIDES OF THE PACKAGE




DETAIL C

SCALE: 2:1



DETAIL B

SCALE: 2:1



BOTTOM VIEW

NOTES: UNLESS OTHERWISE SPECIFIED

- A. PACKAGE STANDARD REFERENCE: JEDEC MO-240, ISSUE A, VAR. AA, DATED OCTOBER 2002.
- B. DIMENSIONS DO NOT INCLUDE BURRS OR MOLD FLASH. MOLD FLASH OR BURRS DOES NOT EXCEED 0.10MM.
- C. ALL DIMENSIONS ARE IN MILLIMETERS.
- D. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
- E. IT IS RECOMMENDED TO HAVE NO TRACES OR VIAS WITHIN THE KEEP OUT AREA.
- F. DRAWING FILE NAME: PQFN08AREV8







### TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

|                          |  |                                       |                  |
|--------------------------|--|---------------------------------------|------------------|
| AccuPower™               | F-PFS™   | OPTOPLANAR®                           |                  |
| AttitudeEngine™          | FRFET®   |                                       | TinyBoost®       |
| Awinda®                  | Global Power Resource™                         | PowerTrench®                          | TinyBuck®        |
| AX-CAP®*                 | GreenBridge™                                   | PowerXS™                              | TinyCalc™        |
| BitSiC™                  | Green FPS™                                     | Programmable Active Droop™            | TinyLogic®       |
| Build it Now™            | Green FPS™ e-Series™                           | QFET®                                 | TINYOPTO™        |
| CorePLUS™                | Gmax™  | QS™                                   | TinyPower™       |
| CorePOWER™               | GTO™   | Quiet Series™                         | TinyPWM™         |
| CROSSVOLT™               | IntelliMAX™                                    | RapidConfigure™                       | TinyWire™        |
| CTL™                     | ISOPLANAR™                                     |                                       | TranSiC™         |
| Current Transfer Logic™  | Making Small Speakers Sound Louder and Better™ | Saving our world, 1mW/W/kW at a time™ | TriFault Detect™ |
| DEUXPEED®                | MegaBuck™                                      | SignalWise™                           | TRUECURRENT®*    |
| Dual Cool™               | MICROCOUPLER™                                  | SmartMax™                             | μSerDes™         |
| EcoSPARK®                | MicroFET™                                      | SMART START™                          |                  |
| EfficientMax™            | MicroPak™                                      | Solutions for Your Success™           | UHC®             |
| ESBC™                    | MicroPak2™                                     | SPM®                                  | Ultra FRFET™     |
|                          | MillerDrive™                                   | STEALTH™                              | UniFET™          |
| Fairchild®               | MotionMax™                                     | SuperFET®                             | VCX™             |
| Fairchild Semiconductor® | MotionGrid®                                    | SuperSOT™-3                           | VisualMax™       |
| FACT Quiet Series™       | MTI®   | SuperSOT™-6                           | VoltagePlus™     |
| FACT®                    | MTX®   | SuperSOT™-8                           | XS™              |
| FAST®                    | MVN®   | SupreMOS®                             | Xsens™           |
| FastvCore™               | mWSaver®                                       | SyncFET™                              | 仙童™              |
| FETBench™                | OptoHiT™                                       | Sync-Lock™                            |                  |
| FPS™                     | OPTOLOGIC®                                     |                                       |                  |

\* Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

### DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. TO OBTAIN THE LATEST, MOST UP-TO-DATE DATASHEET AND PRODUCT INFORMATION, VISIT OUR WEBSITE AT [HTTP://WWW.FAIRCHILDSEMI.COM](http://www.fairchildsemi.com). FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

### ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, [www.fairchildsemi.com](http://www.fairchildsemi.com), under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

### PRODUCT STATUS DEFINITIONS

#### Definition of Terms

| Datasheet Identification | Product Status        | Definition  |
|--------------------------|-----------------------|---|
| Advance Information      | Formative / In Design | Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.   |
| Preliminary              | First Production      | Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. |
| No Identification Needed | Full Production       | Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.   |
| Obsolete                 | Not In Production     | Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.  |

Rev. I73