

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [08-52-0123](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® 254 Crimp Terminal 6459, 22-30 AWG, Bag, Phosphor Bronze Tin \(Sn\)](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-10-07 \(PDF\)](#)

General

| | |
|-------------------------|---|
| Product Family | Crimp Terminals |
| Series | 6459 |
| Application | Signal |
| Crimp Quality Equipment | Yes |
| Overview | KK® Interconnect System - Molex |
| Packaging Alternative | 08-52-0101 (Reel) |
| Product Name | KK® 254 |
| UPC | 800754225885 |

Physical


| | |
|--------------------------------|----------------------|
| Gender | Female |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 0.070/g |
| Packaging Type | Bag |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.57mm max. |
| Wire Size AWG | 22, 24, 26, 28, 30 |
| Wire Size mm² | N/A |

Material Info

| | |
|-----------------|--------------|
| Old Part Number | 6459-(P909)L |
|-----------------|--------------|

Reference - Drawing Numbers

| | |
|-----------------------|----------|
| Product Specification | PS-10-07 |
| Sales Drawing | SD-6459 |



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

6459Series

Use With

2.54mm Pitch KK® Crimp Terminal Housing 2695

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

| Description | Product # |
|-----------------|----------------------------|
| Insertion Tool | 0638120000 |
| Extraction Tool | 0011030022 |
| Hand Crimp Tool | 0638118200 |