

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19193-0202

Status:

Active

Overview:

VersaKrimp™ Terminals and Splices

Description:

VersaKrimp™ Ring Tongue Terminal for 8 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19193

Crimp Quality Equipment

Yes

Mil-Spec

N/A

Overview

VersaKrimp™ Terminals and Splices

Product Name

VersaKrimp™

Type

Ring

UPC

800753039827

Physical

Barrel Type

Closed - Brazed

Insulation

None

Material - Plating Mating

Tin

Net Weight

2.830/g

Packaging Type

Bag

Plating min - Mating

2.540µm

Plating min - Termination

2.540µm

Stud Size

10 (M5)

Termination Interface: Style

Crimp or Compression

Wire Size AWG

8

Wire Size mm²

0.60 - 10.5

Material Info

Old Part Number

D-356-10

Reference - Drawing Numbers

Product Specification

PS-19902-011, PS-19902-013

Sales Drawing

SD-19193-012




image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19193Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hydraulic Dieless Crimping Tool	0638161700
Hand Crimp Tool RHT1080 Hand Crimp Tool	0640013900
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640034400
Manual Putt Pump Hydraulic System, Die set required	0640074400
Die Set (large) for the HHLS Hydraulic Crimper	0192860117
	0192900001

This document was generated on 01/14/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION