

Cornell Dubilier

Cornell Dubilier Marketing, Inc
Liberty, South Carolina
TEL: 864-843-2277 FAX:864-843-3800

Engineering

Catalog Number: DCM202T250BC2A

Customer Part Number: None

Datasheet No.: 3836

Date: 02/03/03

Capacitance: 2000 μ F

Tolerance: - 10% + 50%

Working Volts: 250VDC

Surge Volts: 300VDC

Leakage Current @ 25°C: 2500 μ A

ESR @ 120Hz @ 25°C: 0.052 Ω max.

Ripple Current @ 120 Hz, 85°C: 5.8A

Diameter (D): 2.000 \pm 0.031 inches

Length (L): 4.125 \pm 0.062 inches


Total Length, W/Insulation (TL): 4.203 \pm 0.062 inches

Terminal Spacing (S): 0.875 \pm 0.016 inches

Terminal Thread (T): 10-32 UNF

Insulation: PVC

Operating Temperature: - 40°C ~ +85°C



“Controlled Copy” if viewed on CD Server or if copy is stamped in Red, Otherwise considered as an “Uncontrolled Copy”