

Active Probe

P7225 Datasheet



Features & Benefits

- <math><140\text{ ps}</math> Rise Time (guaranteed)
- 2.5 GHz Bandwidth
- $\leq 0.8\text{ pF}$ Input Capacitance
- 8 $V_{\text{pk-pk}}$ Dynamic Range
- 40 $k\Omega$ Input Resistance
- TekConnect® Interface
- Supports TDS7154/7254 Active Probe Needs by Providing a TekConnect 2.5 GHz, 8 $V_{\text{pk-pk}}$ Dynamic-range Cost-effective Probing Solution for Mid-band Real-time Oscilloscopes
- 10x Attenuation

Applications

- Verification, Debug, and Characterization of High-speed Designs
- Design, Development, and Compliance Testing
- Signal Integrity, Jitter, and Timing Analysis
- Manufacturing Engineering and Test
- Signals with Voltage Swings up to 8 $V_{\text{pk-pk}}$

Selecting the right probe for your application is key to attaining the best signal fidelity in your measurements. Active probes provide truer signal reproduction and fidelity for high-frequency measurements. With our ultra-low input capacitance and high input resistance provided by the P7225, you are able to make measurements with minimal signal distortion. This probe offers a wide 8 $V_{\text{pk-pk}}$ dynamic range to access today's voltage levels.

Performance You Can Count On

Depend on Tektronix to provide you with performance you can count on. In addition to industry-leading service and support, this product comes backed by a one-year warranty as standard.

Characteristics

Physical Characteristics

Rise Time – <140 ps.
 Bandwidth – 2.5 GHz.
 Attenuation – 10x.
 DC Resistance – 40 kΩ.
 Input Capacitance – ≤0.8 pF.
 Dynamic Range – ±4 V.
 Offset Range – ±10 V.
 Interface – TekConnect®.

Ordering Information

Included Accessories – One-year warranty, plus the following:

Product Name/Description	Part Number	Quantity
Ground lead kit – 3 in. and Y Lead Adapter	196-3456-xx	1 Each
SMT KlipChip™ Adapter	206-0364-xx	1
5 Colors, Color Coding Clips	016-1315-xx	1
Pogo Pin Ground (set of 10)	016-1772-xx	1
Square Pin Sockets (set of 10)	016-1773-xx	1
Customizable Ground Lead (set of 5)	196-3482-xx	1
Probe Tips (set of 10)	131-5638-xx	1
SureToe™ Adapter (set of 12)	ST501	1
Instruction Manual	071-1186-xx	1
Probe Carrying Case	016-1879-01	1
Accessory Case	006-7164-xx	1
Wrist Strap	006-3415-04	1
Certificate of Traceability	–	1

Service

Opt. C3 – Calibration Service 3 Years.
 Opt. C5 – Calibration Service 5 Years.
 Opt. D1 – Calibration Data Report.
 Opt. D3 – Calibration Data Report 3 Years (with Opt. C3).
 Opt. D5 – Calibration Data Report 5 Years (with Opt. C5).
 Opt. R3 – Repair Service 3 Years.
 Opt. R5 – Repair Service 5 Years.
 Opt. SILV900 – Standard Warranty Extended to 5 Years.

Recommended Accessories

SMK4, IC Grabber – Order 013-0309-xx (set of 2).



Tektronix is registered to ISO 9001 and ISO 14001 by SRI Quality System Registrar.

Contact Tektronix:

- ASEAN / Australasia** (65) 6356 3900
- Austria** 00800 2255 4835*
- Balkans, Israel, South Africa and other ISE Countries** +41 52 675 3777
- Belgium** 00800 2255 4835*
- Brazil** +55 (11) 3759 7627
- Canada** 1 800 833 9200
- Central East Europe and the Baltics** +41 52 675 3777
- Central Europe & Greece** +41 52 675 3777
- Denmark** +45 80 88 1401
- Finland** +41 52 675 3777
- France** 00800 2255 4835*
- Germany** 00800 2255 4835*
- Hong Kong** 400 820 5835
- India** 000 800 650 1835
- Italy** 00800 2255 4835*
- Japan** 81 (3) 6714 3010
- Luxembourg** +41 52 675 3777
- Mexico, Central/South America & Caribbean** 52 (55) 56 04 50 90
- Middle East, Asia, and North Africa** +41 52 675 3777
- The Netherlands** 00800 2255 4835*
- Norway** 800 16098
- People's Republic of China** 400 820 5835
- Poland** +41 52 675 3777
- Portugal** 80 08 12370
- Republic of Korea** 001 800 8255 2835
- Russia & CIS** +7 (495) 7484900
- South Africa** +41 52 675 3777
- Spain** 00800 2255 4835*
- Sweden** 00800 2255 4835*
- Switzerland** 00800 2255 4835*
- Taiwan** 886 (2) 2722 9622
- United Kingdom & Ireland** 00800 2255 4835*
- USA** 1 800 833 9200

* European toll-free number. If not accessible, call: +41 52 675 3777

Updated 10 February 2011

For Further Information. Tektronix maintains a comprehensive, constantly expanding collection of application notes, technical briefs and other resources to help engineers working on the cutting edge of technology. Please visit www.tektronix.com



Copyright © Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.

27 Jul 2012

60W-16054-7

