

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39-00-0083](#)
Status: **Active**
Overview: [Mini-Fit Jr.™ Power Connectors](#)
Description: [Mini-Fit® Male Crimp Terminal, Tin \(Sn\) over Phosphor Bronze, 16 AWG, Reel](#)

Documents:

Drawing (PDF)	Test Summary TS-5556-002 (PDF)
Product Specification PS-5556-002 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-5558-001 (PDF)	

General

Product Family	Crimp Terminals
Series	5558
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Packaging Alternative	39-00-0084 (Loose)
Product Name	Mini-Fit®
UPC	800753694415

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.120/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	16
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9A
Voltage - Maximum	600V

Material Info

Old Part Number	5558PBT3
-----------------	----------

Reference - Drawing Numbers

Packaging Specification	PK-5558-001
Product Specification	PS-5556-002
Sales Drawing	SD-5558****
Test Summary	TS-5556-002




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

**REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[5558Series](#)

Mates With

[5556 Mini-Fit® Crimp Terminal](#)

Use With

[5559 Mini-Fit Jr.™ Plug Housing](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	0638190900
FineAdjust™ Applicator for Insulation OD 1.80-2.20mm	0639015300

Optimized for 16 AWG Only FineAdjust™ Applicator for Insulation OD 2.60-3.15mm	<u>0639002800</u>
Optimized for 16 AWG Only Extraction Tool T2 Terminator™ for insulation OD 2.60-3.15mm	<u>0011030044</u> <u>0639102800</u>
optimized for 16 AWG only FineAdjust™ Applicator for Insulation OD 2.20-2.45mm	<u>0639003000</u>
Optimized for 16 AWG Only T2 Terminator™ for insulation OD 2.20-2.45mm	<u>0639103000</u>
optimized for 16 AWG only	

This document was generated on 01/23/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION