

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [02-06-7103](#)
Status: **Active**
Overview: Standard .062" Pin and Socket Power Connectors
Description: 1.57mm Diameter, Standard .062" Pin and Socket PC Tail Terminal, Series 1779, Female, with 2.54µm Tin (Sn) Plated Brass Contact, Bag Packaged

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|-------------------------|--|
| Product Family | Crimp Terminals |
| Series | 1779 |
| Application | Power |
| Comments | PC Tail Brass for Standard .062" Housing |
| Crimp Quality Equipment | Yes |
| Overview | Standard .062" Pin and Socket Power Connectors |
| Product Name | Standard .062" |
| UPC | 800753618404 |

Physical


| | |
|--------------------------------|----------------------|
| Gender | Female |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 0.160/g |
| Packaging Type | Bag |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 3.00mm max. |
| Wire Size AWG | N/A |
| Wire Size mm ² | N/A |

Material Info

Old Part Number 1779-(P909)L

Reference - Drawing Numbers

Product Specification RPS-1779-001, RPS-1779-002
 Sales Drawing SD-1779-*



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

1779Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

| | |
|------------------------|----------------------------|
| Manual Extraction Tool | 0011030002 |
|------------------------|----------------------------|