

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [08-55-0101](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® 254 Crimp Terminal, 22-30 AWG, Reel, Selective Gold \(Au\), Nickel \(Ni\) Under Plating](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-10-07 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	2759
Application	Signal
Crimp Quality Equipment	Yes
Overview	KK® Interconnect System - Molex
Packaging Alternative	08-55-0102 (Loose)
Product Name	KK® 254
UPC	800753749900

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.064/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size AWG	22, 24, 26, 28, 30
Wire Size mm²	N/A

Material Info

Old Part Number [2759-\(555\)B](#)

Reference - Drawing Numbers

Product Specification	PS-10-07
Sales Drawing	SD-2759



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[2759Series](#)

Use With

[2695](#) , [5051](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool	0638120000
Mini-Mac™	0638882100
Applicator, Use with Small Wire Insulation Diameter	
Mini-Mac™	0638882000
Applicator, Use with Large Wire Insulation Diameter	
Extraction Tool	0011030022
Terminator Die	0011402265

This document was generated on 01/16/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION