

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

22-01-3137

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 Crimp Housing, Friction Ramp, 13 Circuits

Documents:

3D Model

Packaging Specification PK-2695-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-10-07 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

2695

Application

Signal, Wire-to-Board

Overview

KK® Interconnect System - Molex

Product Name

KK® 254

UPC

800753593473

Physical

Circuits (maximum)

13

Color - Resin

Natural (White)

Flammability

94V-0

Gender

Female

Glow-Wire Compliant

No

Lock to Mating Part

Yes

Material - Resin

Nylon

Net Weight

1.381/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

2.54mm

Pitch - Termination Interface

2.54mm

Polarized to Mating Part

Yes

Stackable

No

Temperature Range - Operating

See Product Specification

Material Info

Old Part Number

2695-13RP

Reference - Drawing Numbers

Packaging Specification

PK-2695-001

Product Specification

PS-10-07

Sales Drawing

SD-2695



image - Reference onlySeries

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

2695Series

Mates With

KK®254 PCB Headers [42375](#) , [42377](#) , [42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With

[2759](#) , [4809](#) KK® Crimp terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION