

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19115-0012](#)  
**Status:** **Active**  
**Overview:** [Solderless Terminals](#)  
**Description:** Avikrimp™ Snap Spade Terminal for 18-22 AWG Wire

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)  
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19115](#)  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [Solderless Terminals](#)  
 Product Name Avikrimp™  
 Type Spade Snap  
 UPC 800753091917

**Physical**


Barrel Type Closed  
 Flammability 94V-2  
 Insulation Nylon (PA)  
 Material - Plating Mating Tin  
 Net Weight 0.824/g  
 Packaging Type Bag  
 Plating min - Mating 4.064µm  
 Plating min - Termination 4.064µm  
 Stud Size 8 (M4)  
 Wire Insulation Diameter 3.60mm max.  
 Wire Size AWG 18, 20, 22

**Material Info**

Old Part Number AA-8714-08

**Reference - Drawing Numbers**

Product Specification PS-19902-011, PS-19902-013  
 Sales Drawing SD-19115-001



**EU RoHS**

**ELV and RoHS Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

19115Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	<a href="#">0640050100</a>
PremiumGrade™ Hand Crimp Tool	<a href="#">0640010100</a>