


# LQP03TN3N0B02#

" # " indicates a package specification code.

Available **General** 125°C Film Thickness 0.33mm max. Tight Tolerance Reflow OK RoHS

< List of part numbers with package codes >  
LQP03TN3N0B02D , LQP03TN3N0B02J , LQP03TN3N0B02B

### Shape



L size	0.6 ± 0.03mm
W size	0.3 ± 0.03mm
T size	0.3 ± 0.03mm
Size code in inch (mm)	0201 (0603)

### Specifications

Inductance	3.0nH ± 0.1nH
Inductance test frequency	500MHz
Rated current (Itemp) (Based on Temperature rise)	450mA
Max. of DC resistance	0.25
Q (min.)	14
Q test frequency	500MHz
Self resonance frequency (min.)	9500MHz
Operating temperature range (Self-temperature rise is not included)	-55 ~ 125

### References


Packaging code	Specifications	Minimum quantity
D	180mm Paper taping	15000
J	330mm Paper taping	50000
B	Packing in bulk	500

Mass (Typ.)	
1 piece	0.0002g


### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ' s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

▪ Inductance-Frequency characteristics (Typ.)



▪ Q-Frequency characteristics (Typ.)



This PDF data has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.