

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19203-0052

Status:

Active

Overview:

High-Temperature Temp Terms Terminals and Splices

Description:

Krimptite™ Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier

Documents:	
Drawing (PDF)	Product Specification PS-19902-015 (PDF)
Product Specification PS-19902-011 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19203
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	High-Temperature Temp Terms Terminals and Splices
Product Name	Krimptite™, Temp-Terms
Type	Ring
UPC	800753049734
Physical	
Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.658/g
Packaging Type	Adhesive Tape on Reel
Stud Size	10 (M5)
Wire Size AWG	14, 16
Wire Size mm²	1.00 - 2.50
Material Info	
Old Part Number	B-S-137-10T
Reference - Drawing Numbers	
Product Specification	PS-19902-011, PS-19902-015
Sales Drawing	SD-19203-017



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19203Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
ATP Perishable	0190270055
Tool Kit used in ATP	
Presses that Process	
Product on Tape	
Mini-Mac™	0638858100
Applicator	