



General Description:

Tough Rubber Insulated cable for medium stress applications in dry and damp conditions, such as hand tools, lightweight workshop tools and welding equipment.

Application:

Electrical connection to be installed in dry or wet condition. It can be used in flexing condition.

Design:

Dimension and other engineering data according to product list Table 2

Conductor	: annealed bare copper in accordance with HD 383 CLASS 5, IEC 60228 and VDE 0295 Class5
Insulation	: EPR EI4 according to DIN VDE 0207 and DIN VDE 0282 part 1
Identification	: Colour Coded to VDE 0293-1, HD 308 S2 or VDE 0293-308
Sheath	: CPE EM3 according to DIN VDE 0207 and DIN VDE 0282 part 1
Sheath Colour	: Orange

Standard Length:

100m reels

Performance Value:

Parameter	Value
Test Voltage	2,000V AC
Operating voltage	300/500kV
Operating temperature (occasional flexing)	-30°C to +60°C
Operating temperature (fixed)	-40°C to 60°C
Bending radius (fixed)	6D (D is cable diameter)
Bending radius (occasional flexing)	20D (D is cable diameter)
Insulation resistance at 20°C	10 ¹² Ω*cm

Table 1

Marking on Cables:

H05RR-F NO. of Core normal section of conductor mmP2P 300/500V xxx m

Product List:

Cable size mm ²	Insulation thick. mm	Sheath Thick. mm	Diameter Min. (mm)	Diameter Max. (mm)
3 × 0.75mm ²	0.6	0.9	6.6	7.2
3 × 1.5mm ²	0.8	1	8.5	9.3
4 × 0.75mm ²	0.6	0.9	7.1	7.8
4 × 1.0mm ²	0.6	0.9	7.5	8.2
4 × 1.5mm ²	0.8	1.1	9.5	10.4

Table 2

Reference:

DIN VDE 0282 part 4

ECD 73/23/EEC (low Voltage Directive)

Part Number Table

Description	Part Number
Multicore, 3 Core, 0.75mm ² , 100m, 500V	PP000665
Multicore, 4 Core, 0.75mm ² , 100m, 500V	PP000666
Multicore, 3 Core, 1.5mm ² , 100m, 500V	PP000667
Multicore, 4 Core, 1.5mm ² , 100m, 500V	PP000669
Multicore, 4 Core, 1mm ² , 100m, 500V	PP000668

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.