

Lithium primary button cell

1. Identification of the product and of the company undertaking

Product details

Trade name: Lithium primary button cell

Voltage: 3.0 V (or multiples of this in case of multi-cell configurations)

Electrochemical system: Lithium metal | organic electrolyte | manganese dioxide

Anode (negative): Lithium metal

Cathode (positive): Manganese dioxide

Туре:	Lithium content per cell:
CR 1025	0,009 g
CR 1216	0,008 g
CR 1220	0,01 g
CR 1225	0,015 g
CR 1616	0,02 g
CR 1620	0,02 g
CR 1632	0,04 g
CR 2016	0,03 g
CR 2016-P	0,03 g
CR 2025	0,05 g
CR 2025-P	0,05 g
CR 2032	0,07 g
CR 2032-P	0,07 g
CR 2320	0,043 g
CR 2430	0,09 g
CR 2450	0,17 g
CR 1/3 N	0,06 g
p 28 pxl	0,05 g

Supplier details

Address: VARTA Microbattery GmbH

Daimlerstr. 1

D-73479 Ellwangen/Jagst

Germany

Emergency telephone number: +49 7961 921 110 (VAC)

Page no.: 1 of 6

Edition: 16.12.2013 Electronically generated document - no signature required.



Legal Remark (U.S.A.)

Safety Data Sheets are a sub-requirement of the Occupational Safety and Health Administration (OSHA) Hazard Communication Standard, 29 CFR Subpart 1910.1200. This Hazard Communication Standard does not apply to various subcategories including anything defined by OSHA as an "article". According to OSHA, Article means a manufactured item other than a fluid or particle: (i) which is formed to a specific shape or design during manufacture; (ii) which has end use function(s) dependent in whole or in part upon its shape or design during end use; and (iii) which under normal conditions of use does not release more than very small quantities, e.g., minute or trace amounts of a hazardous chemical (as determined under paragraph (d) of this section), and does not pose a physical hazard or health risk to employees.

Because all of our batteries are defined as "articles", they are exempted from the requirements of the Hazard Communication Standard.

Legal remark (EU)

These batteries are no "substances" or "mixtures" according to Regulation (EC) No 1907/2006 EC. Instead they have to be regarded as "articles", no substances are intended to be released during handling. Therefore there is no obligation to supply a "safety data sheet according to Regulation (EC) 1907/2006, Article 31".

General remark

This "Safety Information" is provided as a service to our customers. The details presented are in accordance with our present knowledge and experiences. They are no contractual assurances of product attributes.

2. Hazards identification

The battery is sealed hermetically. Thus, the ingredients have no hazard potential, except the battery is violated or dismantled.

If in case of mistreatment the ingredients are released, a spontaneously flammable gas mixture may be released under certain circumstances (measures according to chapter 4 to 6).

Attention: If batteries are treated wrong the danger of burns or bursts occurs. Batteries must not be heated above 100°C or incinerated. The battery contents must not get in contact with water. If the negative electrode gets in contact with water or humidity hydrogen gas is formed, which may inflame spontaneously.

3. Composition/information on ingredients

Ingredients

Contents	CAS No.	Hazard Categories	Hazard Statements	Material
1 - 3 %	7439-93-2	Water-react. 1	H260	Lithium
		Skin Corr. 1B	H314	
13 - 40 %	1313-13-9	Acute Tox. 4	H302	Manganese dioxide
			H332	_
3 - 9 %		Flam. Liq. 2	H225	Organic electrolyte,
		Eye Irrit. 2	H319	consisting of lithium
		Acute Tox. 4	H332	perchlorate, organic
		Repr. 1B	H360FD	carbonates and ethers

Full text of Hazard statements: see section 16.

Heavy Metals

Contents	CAS No.	Material
< 1 mg/kg	7440-43-9	Cadmium
< 10 mg/kg	7439-92-1	Lead
< 0,1 mg/kg	7439-97-6	Mercury (none intentionally introduced, see Chapter 12)
< 5 mg/kg		Hexavalent Chromium (Cr6+)

Other Ingredients

Contents	CAS No.	Material
33 - 74 %		Steel and nickel
3 - 10 %		Plastic

Page no.: 2 of 6

Edition: 16.12.2013 Electronically generated document - no signature required.



SVHC substances according to REACH (Article 33)

 Contents
 EC No.
 CAS No.
 Material

 > 0.1 %
 203-794-9
 110-71-4
 1,2-dimethoxyethane; ethylene glycol dimethyl ether (EGDME)

For information to allow safe use: see section 7.

4. First-aid measures

Measures at accidental release

After inhalation: Fresh air. Seek for medical assistance.

After skin contact: Remove solid particles immediately. Flush affected areas with plenty of

water (at least 15 min.). Remove contaminated cloth immediately. Seek for

medical assistance.

After eye contact: Flush the eye gently with plenty of water (at least 15 min.). Seek for medical

assistance.

After ingestion: Drink plenty of water. Avoid vomiting. Seek for medical assistance.

No trials for neutralization.

5. Fire-fighting measures

Suitable extinguishing media: Metal fire extinction powder, rock salt or dry sand shall be used.

In case only water is available, it can be used in large amounts.

Extinguishing media with limited

suitability:

Carbon dioxide (CO₂) is not suitable. Water in small quantities may have adverse effects.

Protective clothing including breathing apparatus.

Special protection equipment during

fire-fighting: Special hazard:

Cells may explode and release metal parts.

At contact of anode material with water extremely flammable hydrogen gas

and caustic liquid are released.

Attention: Do not let used extinguishing media penetrate into surface water or ground

water. Dispose off properly.

6. Accidental release measures

Person related measures: Wear personal protective equipment adapted to the situation (protection gloves,

cloth, face protection, breathing protection).

Environment protection measures: Bind released ingredients with powder (rock salt, sand).

Dispose off according to the local law and rules.

Avoid leached substances to penetrate into the earth, canalization or water.

Treatment for cleaning: If battery casing is dismantled, small amounts of electrolyte may leak. Package

the battery tightly including ingredients together with lime, sand or rock salt. Then

clean with water.

Page no.: 3 of 6

Edition: 16.12.2013 Electronically generated document - no signature required.



7. Handling and storage

Guideline for safe handling: Always follow the warning information on the batteries and in the manuals of

devices. Only use the recommended battery types.

Keep batteries away from children.

For devices to be used by children, the battery casing should be protected

against unauthorized access.

Unpacked batteries shall not lie about in bulk.

In case of battery change always replace all batteries by new ones of identical

type and brand.

Do not swallow batteries. Do not throw batteries into water. Do not throw batteries into fire. Do not short-circuit batteries. Do not recharge primary batteries.

Do not open or disassemble batteries.

Storage: Storage preferably at room temperature (approx. 20°C). Avoid large

temperature changes. Avoid direct sunlight. At higher temperature the electrical

performance may be reduced.

Storage of unpacked batteries can cause short circuit and heat generation.

Storage category

It is recommended to consider the "Technical Rule for Hazardous Substances according to TRGS 510: TRGS 510 - Storage of hazardous substances in nonstationary containers" and

to handle lithium primary cylindrical cells according to storage category 11

("combustible solids").

Storage of large amounts: Follow the recommendations of the German Insurance Association (GDV -

"Gesamtverband der Deutschen Versicherungswirtschaft e.V.") concerning

lithium batteries:

http://vds.de/fileadmin/vds_publikationen/vds_3103_web.pdf

In case of storage of large amounts (used storage volume > 7 m3 and/or more than 6 pallets) batteries shall be stored in fire-resistant or separated rooms or areas (e.g. warehouse or container for hazardous materials). Mixed storage with other products is not allowed. The storage area shall be monitored by an automatic fire detection system, connected to a permanently manned place. A fire-extinguishing system shall reflect the extinguishing agents mentioned in

chapter 5.

8. **Exposure controls/personal protection**

Under normal conditions (during discharge) release of ingredients does not occur.

9. Physical and chemical properties

Not applicable if closed.

10. Stability and reactivity

Dangerous reactions: When heated above 100°C the risk of rupture occurs.

11. **Toxicological information**

Under normal conditions (during charge and discharge) release of ingredients does not occur. In case of accidental release see information in chapter 2.

Swallowing of a battery can be harmful. Call the local Poison Control Centre for advice and follow-up.

Page no.: 4 of 6

Edition: 16.12.2013 Electronically generated document - no signature required.



12. Ecological information

Lithium primary button cells do not contain heavy metals as defined by the European directives 2006/66/EC Article 21; they comply with the chemical composition requirements of this Directive.

Mercury has not been "intentionally introduced (as distinguished from mercury that may be incidentally present in other materials)" in the sense of the U.S.A. "Mercury-Containing and Rechargeable Battery Management Act" (May 13 1996).

The Regulation on Mercury Content Limitation for Batteries promulgated on 1997-12-31 by the China authorities including the State Administration of Light Industry and the State Environmental Protection Administration defines 'low mercury' as 'mercury content by weight in battery as less than 0.025%', and 'mercury free' as 'mercury content by weight in battery as less than 0.0001%'. And therefore: Varta lithium primary button cells/batteries belong to the category of mercury-free battery (mercury content lower than 0.0001%).

13. Disposal considerations

USA: Lithium primary button cells are classified by the federal government as non-hazardous waste and are safe for disposal in the normal municipal waste stream.

In the European Union, manufacturing, handling and disposal of batteries is regulated on the basis of the DIRECTIVE 2006/66/EC OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 6 September 2006 on batteries and accumulators and waste batteries and accumulators and repealing Directive 91/157/EEC. Customers find detailed information on disposal in their specific countries using the web site of the European Portable Batteries Association (http://www.epbaeurope.net/legislation_national.html).

Importers and users outside EU should consider the local law and rules.

In order to avoid short circuit and heating, used lithium primary button cells should never be stored or transported in bulk. Proper measures against short circuit are:

- Storage of batteries in original packaging
- Coverage of the terminals
- Embedding in dry sand

14. Transport information

General considerations

Lithium primary button cells manufactured by VARTA Microbattery are considered to be UN3090 Lithium Metal Batteries and are tested according to 38.3 of the "UN Manual of Tests and Criteria" for compliance with the requirements of special provisions ADR 188, IMDG 188, DOT / 49 CFR § 172.102, and the General Requirements of IATA DGR packing instruction 968. Positive test results as well as other relevant information required for transportation are stated in dedicated "Declarations of Conformity".

Transportations of cells or batteries packed with equipment or contained in equipment have to follow the appropriate regulations for UN3091.

USA

Primary (non-rechargeable) lithium batteries and cells are forbidden for transport aboard passenger carrying aircraft. The outside of each package that contains primary (non-rechargeable) lithium batteries or cells must be marked "PRIMARY LITHIUM BATTERIES-FORBIDDEN FOR TRANSPORT ABOARD PASSENGER AIRCRAFT" on a background of contrasting color.

Page no.: 5 of 6

Edition: 16.12.2013 Electronically generated document - no signature required.



IEC 60086-1

Code of practice for packaging and shipment of primary batteries given in IEC 60086-1:

The packaging shall be adequate to avoid mechanical damage during transport, handling and stacking. The materials and pack design shall be chosen so as to prevent the development of unintentional electrical conduction, corrosion of the terminals and ingress of moisture.

Shock and vibration shall be kept to a minimum. For instance, boxes should not be thrown off trucks, slammed into position or piled so high as to overload battery containers below. Protection from inclement weather should be provided.

15. Regulatory information

Marking consideration: For the state of California these batteries have to be marked as "containing

perchlorate".

According to "DIRECTIVE 2006/66/EC OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 6 September 2006 on batteries and accumulators and waste batteries and accumulators and repealing Directive 91/157/EEC" the batteries have to be marked with the crossed bin. Due to the size of the products the battery need not be marked but a symbol measuring at least 1 x 1 cm shall be

printed on the packaging..

International safety standards: The basis cells are recognized components according to UL 1642.

Water hazard class: The regulations of the German Federal Water Management Act (WHG) are not

applicable as Lithium primary batteries are articles and not substances, thus there is no risk of water pollution, except the batteries are violated or dismantled.

16. Other information

Full text of Hazard Statements referred to under section 3

H225	Highly flammable liquid and vapour.
H260	In contact with water releases flammable gases which may ignite spontaneously.
H302	Harmful if swallowed.
H314	Causes severe skin burns and eye damage.
H319	Causes serious eye irritation.
H332	Harmful if inhaled.
H360FD	May damage fertility. May damage the unborn child.

Note: Date of issue of the transport regulations: ADR 2013, RID 2013, IATA 2014

(55th edition), IMDG 2012, DOT / 49 CFR 2013.

Latest covered modification of the European Battery Directive 2006/66/EC:

Directive 2013/56/EU.

Issued by: VARTA Microbattery GmbH

Quality / Environmental Management

Contact person: Dr. Rainer Jostes

Tel. +49-7961-921-680 Fax +49-7961-921-73680

E-Mail: rainer.jostes@varta-microbattery.com

Updates: Current SDS can be downloaded from VARTA's web page following the link:

http://www.varta-microbattery.com/en/news-downloads/downloads.html

Page no.: 6 of 6

Edition: 16.12.2013 Electronically generated document - no signature required.