# EVOLUTION®

www.evolutionsteel.com

#### **EVO180 CUTTING THROUGH STEEL BOX SECTION**



#### **Cut: STEEL WITHOUT HEAT, BURRS OR COOLANT**

OPTIONAL BLADES CUT STAINLESS STEEL, ALUMINIUM & WOOD

**BLADES** COLOUR DIA. BORE TEETH M.RPM Steel 180mm 20mm 36 3500 Stainless Steel\* 180mm 20mm 3500 Aluminium 180mm 20mm 54 3500 Wood 180mm 20mm 30 3500

# **EV0180**

#### 180mm TCT STEEL CUTTING CIRCULAR SAW

New and improved! The EV0180 now features 0-45° bevel tilt for more cutting versatility and an autodebris collection system. The overall performance is still just as impressive; it will cut Steel quickly and cleanly without any heat, burr or coolant. Robust and highly durable, typically a blade will cut up to 80m\* of 6mm before a replacement is required. Ideal for cutting steel plate, box section, cast iron pipe, scaffolding, cladding and roofing.

#### SUPPLIED WITH -

180mm TCT Blade, Guide Rail. Carry Case & 12 Months Warranty.

#### TECHNICAL SPECIFICATIONS

Motor · 1100W Max Depth Cut: 55mm Max Depth Cut 45°: 35mm Max Cutting Thickness (Solid Steel Plate): 6mm Speed: 3500rpm Weight: 6.5kg

**IMPROVED** 





**CUTS 6MM STEEL PLATE** 



**CUTS ALUMINIUM** 



**AUTO-DEBRIS COLLECTION** 

#### NEW DESIGN, IMPROVED PERFORMANCE.

\*Evolution Internal Test Data.

\*Machine is Stainless Steel capable.

# **EVO230 CUTTING THROUGH 12MM INDUSTRIAL STEEL PLATE** ULTRA HIGH GRADE CARRIDE **ADVANCED** PERFORMANCE

#### Cut: STEEL WITHOUT HEAT, BURRS OR COOLANT

OPTIONAL BLADES CUT STAINLESS STEEL, ALUMINIUM & WOOD

BLADES COLOUR BORE TEETH M.RPM Steel 25.4mm 2700 Stainless Steel\* 25 4mm 60 2700 Aluminium 2700 Wood 2700 25.4mm

\*Machine is Stainless Steel capable.

# **EV0230**

#### 230mm TCT STEEL CUTTING CIRCULAR SAW

The EV0230 displays incredible cutting capabilities through the toughest applications. The powerful 1750W motor allows this machine to breeze through mild steel without heat build-up, burr or the use of coolant. Features include a useful laser guide to assist with accurate cutting and bevel tilt enhancing the versatility of the saw. The

maximum depth of cut is an amazing 84mm whilst offering a cutting capacity of 12mm plate thickness. It is economical in its performance tootypically a long-life blade cuts up to 80m of 8mm steel plate\*.

#### **SUPPLIED WITH:**

230mm TCT Steel Blade, Side Handle, Fence Guide, 2 x Battery, Wrench Attached, Carry Case & 12 Months Warranty.

#### **TECHNICAL SPECIFICATIONS:**

Motor: 1750W

Maximum Box Cutting Capacity 90° (6mm Wall): 84mm Maximum Box Cutting Capacity 45° (6mm Wall): 53mm Maximum Cutting Depth (Mild Steel Plate): 12mm Speed: 2700rpm | Weight: 9kg

THE PREMIUM PERFORMANCE CIRCULAR SAW FOR STEEL CUTTING

HIGH TORQUE MOTOR

**LASER** 

GUIDE



**TILTING ADJUSTMENT** 



84MM DEPTH OF CUT

\*Fvolution Internal Test Data

#### **EV0355 SLICING THROUGH STEEL BOX SECTION**



### Cut: STEEL WITHOUT HEAT, BURRS OR COOLANT OPTIONAL BLADES CUT STAINLESS STEEL & ALUMINIUM

BLADES COLOUR BORE TEETH M.RPM Steel 305mm 25 4mm 60 1450 1450 Steel 25.4mm Stainless Steel\* 90 1450 Aluminium 1450 25 4mm

\*Machine is Stainless Steel capable.

# **EV0355**

#### 355mm TCT STEEL CUT OFF SAW

The incredible EV0355 Cut Off Saw slices through mild Steel with ease, producing no burr, leaving an instantly workable finish. Utilising a powerful 2200W motor, the EV0355 can handle even the most demanding on-site jobs. The cleanest, quickest and most economical way of cutting mild Steel. Ideal for cutting box section, beams, cast iron pipe, scaffolding and metal studding.

#### **SUPPLIED WITH:**

355mm TCT Steel Blade, Guard, Jig Plate, 8mm Hex Wrench, 6mm Hex Wrench & 12 Months Warranty.

#### **TECHNICAL SPECIFICATIONS:**

Motor: 2200W

Max Box Section (6mm Wall 90°): 120mm x 120mm Max Square (6mm Wall 45°): 89mm x 89mm Rectangle (6mm Wall 90°): 95mm x 180mm Rectangle (6mm Wall 45°): 78mm x 110mm Round (6mm Wall 90°): 130mm

Round (6mm Wall 45°): 105mm Speed: 1450rpm | Weight: 23kg



VICE JAVV



**SIDE VIEW** 



**COLLECTION TRAY** 

#### THE EVO355 CAN HANDLE EVEN THE MOST DEMANDING ON-SITE JOBS

\*Evolution Internal Test Data.

#### **EVO42 DRILLING THROUGH STEEL I-BEAM**



Ideal For: BRIDGES • I-BEAMS • FRAMEWORK

INDUSTRIAL STEEL MAGNETIC DRILL

PREMIUM GRADE 3 PIECE CUTTER SET (25mm DEPTH)
Includes 14, 18 & 22mm Cutters & Pilot Pins.

PREMIUM GRADE 6 PIECE CUTTER SET (25mm DEPTH)
Includes 12, 14, 16, 18, 20 & 22mm Cutters & Pilot Pins,

# **EV042 MAG DRILL**

#### 42MM INDUSTRIAL MAGNETIC DRILLING SYSTEM

This incredible Magnetic Drill is deceptive in its capabilities; although small in size it revels in heavy-duty industrial and fabrication work. Versatile, accurate and portable, with strong magnetic adhesion (1300Kg f). The cuts are precise and clean due to an optimised rotation speed (450rpm) and all popular broaching capacities are covered (12-42mm). Twist drills can be attached and the innovative adjustable head enables twist drills to be used to full capacity.

#### **SUPPLIED WITH:**

Oil Coolant System, Hex Keys 2, 3, 4mm, 3 Handles, 1 Shipping Guard, Safety Strap, HTA47 Cutter Adapter, & 12 Months Warranty.

#### TECHNICAL SPECIFICATIONS:

Motor: 1200W | Weight: 10.9kg Max Cutter Diameter: 42mm Max Cutting Depth: 50mm Speed (No Load): 450rpm

Magnetic Adhesion : 1300Kg f Cutter Retainer Internal Diameter :

19mm Weldon Shank

QUICK & EASY

ADJUSTABLE

HEAD POSTION!





INTEGRATED COOLANT SYSTEM



**UP TO 42MM CUTTING CAPACITY** 



**CUTS HOLES IN 15 SECONDS** 

**UNMATCHED IN PRICE RELATED PERFORMANCE** 

#### PREMIUM QUALITY, PREMIUM PERFORMANCE



#### Don't Forget: THE CUTTER SETS

PREMIUM GRADE 3 PIECE CUTTER SET (25mm DEPTH)
Includes 14, 18 & 22mm Cutters & Pilot Pins.

PREMIUM GRADE 6 PIECE CUTTER SET (25mm DEPTH)
Includes 12, 14, 16, 18, 20 & 22mm Cutters & Pilot Pins.

PREMIUM GRADE 6 PIECE CUTTER SET (50mm DEPTH)
Includes 12, 14, 16, 18, 20 & 22mm Cutters & Pilot Pins,

### **CYCLONE ANNULAR CUTTERS**

Cyclone cutters are guaranteed to outperform annular cutters made out of HSS, Cobalt, or Tini Coated Cutters. Because...

- The Tini Coating on HSS annular cutters increases the cost of the cutter but only enhances the cutter's appearance.
- HSS M-2 Annular Cutters can only be heat treated up to 64 RC before they become too brittle.
- Cobalt Annular cutters can only be heat treated up to 66 RC before they become too brittle.
- Cyclone Premium Annular Cutters can be heat treated up to 68 RC and they still have tempered hardness.

A higher RC rating without brittleness means more holes cut per sharpening. Cyclone Premium Annular Cutters are available in stock for immediate delivery in the following size ranges: Short Series - 25mm length, 12mm - 65mm Diameter Long Series - 50mm length, 12mm - 65mm Diameter
















| DIA. | 25mm  | 50mm  |
|------|-------|-------|
| 12mm | HT12S | HT12L |
| 13mm | HT13S | HT13L |
| 14mm | HT14S | HT14L |
| 15mm | HT15S | HT15L |
| 16mm | HT16S | HT16L |
| 17mm | HT17S | HT17L |
| 18mm | HT18S | HT18L |
| 19mm | HT19S | HT19L |
| 20mm | HT20S | HT20L |
| 21mm | HT21S | HT21L |
| 22mm | HT22S | HT22L |
| 23mm | HT23S | HT23L |
| 24mm | HT24S | HT24L |
| 25mm | HT25S | HT25L |
| 26mm | HT26S | HT26L |
| 27mm | HT27S | HT27L |
| 28mm | HT28S | HT28L |
| 29mm | HT29S | HT29L |

HT30S

HT31S

SPILOT

30mm

31mm

Pilot Pin

HT30L

HT31L

I PII OT



**CUT HOLES IN 15 SECONDS** 



NO PRE-STEP DRILLING



**FREE PILOT PIN** 

CUTTER SIZES ALSO AVAILABLE FROM UP TO 65MM, IN 1MM INCREMENTS\*

# CYCLONE MAGNETIC CHIPPING COLLECTOR

Fabricating in Steel can be a messy business, Evolution has the perfect tool to quickly clean up your metal shavings & scrap pieces. Simply wave the Magnetic Chipping Collector over the metal shavings to pick them up, carry them over to your scrap barrel, pull the plunger and the shavings are neatly deposited. The Cyclone's magnet is strong enough to quickly clean up your biggest mess of metal shavings.



#### THE QUICK & EASY WAY TO CLEAN YOUR WORKSPACE

# CYCLONE2 MAGNETIC CHIPPING SWEEPER

Perfect for workshops, garages, driveways & yards. In addition to the Cyclone Magnetic Chipping Collector, Evolution also offer this superb Magnetic Chipping Sweeper. Simply sweep over ferrous metal debris, then slide the collar to neatly deposit the waste. This ensures that awkward metal objects, often missed by a conventional brush, are gathered easily, especially on an uneven surface.



GATHERS AWKWARD OBJECTS OFTEN MISSED BY A BRUSH

#### **MAGNETIC DRILLING ACCESSORIES\***

#### EV042 ACCESSORIES

HTA47 Chuck Adaptor

#### MESSON & MESONN ACCESSORIES

HTA153 Chuck & Key 1/2"\*

HTA45 Chuck Adaptor V1\*

\*\*Required To Use Chuck For Version

HTA46 Adaptor V2 Quick Release\*

\*Both Required To Use Chuck With These Machines

0 - 30mm Countersink

#### ME5000/2 ACCESSORIES

HTA030

HTA51 Chuck & Key 5/8"\*

HTA46 Adaptor V2 Quick Release\*

\*Both Required To Use Chuck With This Machine

HTA57 0 - 50mm Countersink

#### **ME7500 ACCESSORIES**

HTA54 Chuck & Key 5/8"\*

HTA53 Chuck Arbor\*

\*Both Required To Use Chuck With This Machine
HTA57 Countersink 0 - 50mm

HTAM24 Tapping Chuck
HTACOLL Tapping Collet

#### **GENERAL ACCESSORIES**

HTA210 No 2M/T Arbor Adaptor\*
HTA310 No 3M/T Arbor Adaptor\*

\*Pillar Drill Arbor Adaptors In Both 2M/T & 3M/T

#### **CUTTING FLUID FOR MAGNETIC DRILLS**

FLUID 5L Cutting Fluid
FLUID2 500ml Cutting Fluid

\*All magnetic drilling accessories prices are SSP EXC VAT.



CHUCKS & KEYS



CUTTING FLUI



**CHUCKS & ADAPTORS** 



CHUCK ARBORS



## Ideal For: WELDS • CUTTING GROOVES WITH ACCURATE, CLEAN RESULTS



#### Don't Forget: THE ACCESSORY KIT

#### **EVO27 DIE GRINDER 25 PIECE ACCESSORY KIT**

This comprehensive kit enhances the versatility of the **EV027 DIE GRINDER** and can be used on other makes of Die Grinder. British made with the highest quality Carbide Burrs, Flap Wheels & Flexible Cut Off Discs. Contains 1 x Mandrel. 4 x Carbide Burr. 3 x Flap Wheel & 17 x Flexible Cut Off Disc.

### **EVO27** 500W INDUSTRIAL STEEL DIE GRINDER

This handy machine is perfect for smoothing and tidying welds and burrs on metal applications, as well as cutting grooves. It's also well suited towards fine work, even in tight areas; the EVO27 can polish and buff the inside of cylindrical objects! With a slim and compact design the tool fits comfortably in the hand and the robust metal gear housing means it can easily cope with the rigours of site-work. Features include a lock on/off switch and a grinding spindle with extremely accurate bearing for precise results.

#### SUPPLIED WITH -

1 x 6mm Collet, 1 x 1/4" Collet, 2 x Spanner (Collet) & 12 Months Warranty.

#### TECHNICAL SPECIFICATIONS:

Motor : 500W Spindle Collar Diameter : 6mm (1/4") Collet Capacity : 35mm Speed (No Load) : 29,000rpm Weight : 1.67kg



4 x CARBIDE BURR

MANDREI



17 x FLEXIBLE CUT OFF DISC

DON'T FORGET

25 PIECE

**ACCESSORY KIT** 

25 PIECE ACCESSORY KIT, FOR FURTHER DETAILS PLEASE VISIT WWW.EVOLUTIONSTEEL.COM



**CUTTING GROOVES** 

Your local Evolution stockist:

Pioneering dry cutting technology without heat, burrs or coolant.

CALL 0870 609 2297