


KEMET Part Number: C321C104K5R5HA
(C321C104K5R5HA)

Capacitor, ceramic, 0.1 uF, +/-10% Tol, 50 V, X7R, Lead Spacing=0.25"



Dimensions (in)

Symbol	Dimension	Tolerance
L	0.20	MAX
H	0.26	MAX
T	0.12	MAX
S	0.25	+/-0.03
LL	0.28	MIN
F	0.02	+0.004/-0.001

Packaging Specifications

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	500

General Information

Supplier:	KEMET
Application:	General Purpose
Temperature Coefficient:	X7R
Body Type:	Radial Conformal
Lead Type:	HockeyStick
Termination Type:	Tin-Lead (SnPb)
RoHS:	No

Specifications

Capacitance:	0.1 uF
Voltage:	50 V
Tolerance:	+/-10%
Temperature Range:	-55/+125C
Failure Rate:	NA
Dissipation Factor:	2.5%
Insulation Resistance:	10 GOhm
Dielectric Strength:	125 V