











Angled Head Small

Length 115 mm

Model	L	A	B	C	D	Max. Cu	Weight	Description
 572E 	115 mm	18 mm	10,5 mm	6,5 mm	6,5 mm	ø 0,6 mm	68 g	<p>✂ 40°, flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable</p> <p>Tip cutter. Medium size. Relieved jaws for easier access.</p>
 593AE 	115 mm	20 mm	10,5 mm	6,5 mm	4 mm	ø 1,0 mm	68 g	<p>✂ 50°, flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable</p> <p>Tip cutter. Cuts easily DIL leads from the rear. Cuts pins on dense PCB. Ideal maintenance tool.</p>
 582E 	115 mm	19 mm	10,5 mm	6,5 mm	7 mm	ø 1,0 mm	68 g	<p>✂ 45°, flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable</p> <p>Tip cutter medium size. A must when working on PCB's, cutting component leads. Also ideal for rework.</p>
 582EW 	115 mm	19 mm	10,5 mm	6,5 mm	7 mm	ø 1,0 mm	70 g	<p>✂ 45°, flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable, retention clip</p> <p>Same as 582E but with retention clip, holds wire scraps after cutting.</p>

Length 120 mm

Model	L	A	B	C	D	Max. Cu	Weight	Description
 555E 	120 mm	21 mm	10,5 mm	6 mm	6,5 mm	ø 1,2 mm	68 g	<p>✂ 40°, flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable</p> <p>Tip cutter. Strong version.</p>