IEC Cylindrical Fuse Holders

The innovative and comprehensive Modulostar® range of Mersen fuse-holders. Modular fuse-holders are finger-safe under IEC standards to an IP20 grade of protection, including fuse changing (with the flick of a finger). Modular fuse-holders are available in 1, 2, 3 or 4 poles, with or without visual blown fuse indicator, in IEC version or IEC + UL version. Multi-pole units can also be field assembled by ordering pin-ties assembly kit. In size 14 or 22, the range also offers the possibility to use microswitches (supplied with the holders or ordered separately) to allow remote indication. Modulostar® range is made of tough and durable thermoplastic or thermoset material.

Features Benefits

- Finger safe
- Degree of protection: IP20
- Optional visual blown fuse indicator
- DIN rail mounting
- Modular design
- Lockable
- Multi-pole assembly kit available
- Sealable in closed and open position
- Plastic material UL94V2 mini
- Flame retardant materials with glow wire flammability index to 960°C
- Schock and vibration tested for marine and railway applications

Applications

- All circuits up to 690V for protection of motors, transformers, low voltage distribution, control circuits, drive protection
- Non-load operation

Technical data overview

Voltage AC	690 VAC
Voltage DC	690 VDC
Amper (A)	32 A
SCCR	200kA
Mounting	Installation on to DIN rails to EN 60715
Product Size	For cylindrical fuse links 10.3x38.1 AM, gG and 10.3x38 Mersen Protistor and HP6M fuse-links
Number of Poles	1 to 4 poles





Standards

IEC 60269-2 and IEC 60947-3 Compliance

RoHS Compliant

Plastic material: NF 16101 & 16102 Requirement 2 Compliant

Shock and vibration tested for marine and railway applications















Product range



CMS101



CMS102



CMS103



CMS103N

Modulostar® fuse-holders for 10.3x38.1 fuse-links, without indicator

Catalog number	Reference number	Number of poles/ phases	Design	Weight	Package
CMS810N	D305006	N	CMS10 neutral conductor	65.8 g	12
CMS101	T305020	1	CMS10 single pole	61.3 g	12
CMS101N	V305021	1 + N	CMS10 single pole + neutral conductor	131.6 g	6
CMS102	W305022	2	CMS10 double pole	121.6 g	6
CMS103	X305023	3	CMS10 triple pole	197.5 g	4
CMS103N	Y305024	3 + N	CMS10 triple pole + neutral conductor	263.3 g	3
CMS104	Z305025	4	CMS10 quadruple pole	243.3 g	3



Modulostar® fuse-holders for 10,3x38,1 fuse-links, with indicator

Catalog number	Reference number	Number of poles/ phases	Design	Weight	Package
CMS101I	A305026	1	CMS10 single pole	60.8 g	12
CMS101NI	B305027	1 + N	CMS10 single pole + neutral conductor	131.6 g	6
CMS102I	C305028	2	CMS10 double pole	121.6 g	6
CMS103I	D305029	3	CMS10 triple pole	182.5 g	4
CMS103NI	E305030	3 + N	CMS10 triple pole + neutral conductor	263.3 g	3
CMS104I	F305031	4	CMS10 quadruple pole	243.3 g	3

Modulostar® CMS10 Modular fuse-holders



Technical Data

	CMS10	CMS10I
Size	10x38	10x38
Number of poles/phases	1, 1+N, 2, 3, 3+N, 4	1, 1+N, 2, 3, 3+N, 4
Conventional free air thermal current with fuse links I _{th}	32 A	32 A
Power dissipation at I _{th}	3 W	3 W
Utilisation category	AC20B/DC20B	AC20B/DC20B
Rated insulation voltage U _i	690 V	690 V
SCCR	200 kA	200 kA
Rated impulse withstand voltage U _{imp}	6 kV	6 kV
Degree of protection	IP 20	IP 20
Voltage limit for blown fuse indicator	-	230 to 690V AC/DC
Indication System	-	with indicator
Connection	Max. tightening torque: 2.2Nm (19lbsin) Rigid wire = 1-16mm² (16-6AWG) Multistrand wire = 0.75-10mm² (18-8AWG) PZ2 or flat 5.5x1mm screw drivers recommended (max. diameter 6mm)	Max. tightening torque: 2.2Nm (19lbsin) Rigid wire = 1-16mm² (16-6AWG) Multistrand wire = 0.75-10mm² (18-8AWG) PZ2 or flat 5.5x1mm screw drivers recommended (max. diameter 6mm)
Operating temperature	-25°C to 60°C	-25°C to 60°C
Storage temperature	-25°C to 80°C	-25°C to 80°C
Vibration	Withstand on the 3 main axis*: Sinusoidal vibration testing according to IEC 60068-2-6 2 to 13Hz x= 1 mm peak 13 to 100Hz y= 0.7g peak according to french marine application Random vibration testing according to IEC 61373 Category 1 Class B	Withstand on the 3 main axis*: Sinusoidal vibration testing according to IEC 60068-2-6 2 to 13Hz x= 1 mm peak 13 to 100Hz y= 0.7g peak according to french marine application Random vibration testing according to IEC 61373 Category 1 Class B
Shock	Shock testing according to IEC 61373 Category 1 Class B Shock testing according to IEC 60068-2-27 15g/11ms/18 shocks * for specific usage please contact us	Shock testing according to IEC 61373 Category 1 Class B Shock testing according to IEC 60068-2-27 15g/11ms/18 shocks * for specific usage please contact us

Specific usage conditions

Ambient temperature	>20°C	30°C	40°C	50°C	60°C
Derating factor (I _e)	1	0.95	0.9	8.0	0.7


No of poles (side by side)	1 to 3	>/= 4
Derating factor of current (I _{th})	1	0.9

Nominal current of fuse-link gR	20 A	25 A	30 A	32 A
Max. operational current in fuse-holder	19 A	22 A	25 A	27 A
Cable wire section	2.5 mm ²	4 mm²	6 mm ²	6 mm ²



Dimensions

Dimensions in mm



Accessories



CMS8010PAK + fuse-holder

Kit for multi phase connection

Catalog number	Reference number	Description	Weight kg¹)	Package
CMS810PAK	Z233725	Links for connection of multipole units	0,00058	12

Locking devices



TAGLOCKCMS810

LOCK

Catalog number	Reference number	Description	Weight kg ¹⁾	Package
TAGLOCKCMS810	A235773	Locking kit (Tag and lockout)	0.009	1
LOCK	M223525	Padlock	0.042	1

Package

50

50

50

50

Weight

0.010

0.010

0.023

0.023

Application

Max. rms current 90A

Max. rms current 90A

Max. rms current 90A

Max. rms current 90A

Accessories





TBB1A

TBB1C





TBB23A

TBB23C

Power supply Catalog

TBB1A

TBB1C

TBB23A

Reference

number

D210315

E210316

F210317

TBB23C G210318


Description

1 phase axial incoming power supply

1 phase lateral incoming power supply

2 & 3 phases axial incoming power supply

2 & 3 phases lateral incoming power supply





CMS810BB4F3



CMS810BB3F4



CMS810BB2F6



CMS810BB1F13