

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

22-16-2151

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 PC Board Connector, Right Angle, End-to-End Stackable, 0.50µm Gold (Au), 15 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-10-07 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Receptacles

Series

4455

Application

Board-to-Board, Signal

Overview

KK® Interconnect System - Molex

Product Name

KK® 254

UPC

800753737617

Physical

Circuits (Loaded)

15

Circuits (maximum)

15

Color - Resin

Natural (White)

Flammability

94V-0

Glow-Wire Compliant

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

No

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Gold

Material - Resin

Nylon

Net Weight

1.582/g

Number of Rows

1

Orientation

Right Angle

PC Tail Length

3.35mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Tray

Pitch - Mating Interface

2.54mm

Pitch - Termination Interface

2.54mm

Plating min - Mating

0.508µm

Plating min - Termination

0.051µm

Polarized to PCB

Yes

Temperature Range - Operating

See Product Specification

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

2.5A

Grounding to PCB

No

Voltage - Maximum

250V

Solder Process Data




image - Reference only

Series

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
4455Series

Mates With
42153 KK® Wire-to-Board Header, 4094 KK® Wire-to-Board Header, 42376 KK® Header, 42375 KK® Header, 42377 , 42152 KK® Wire-to-Board Header, 4030 KK® Wire-to-Board Header, 4380 KK® Header

Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235

Material Info

Old Part Number	A-4455-AZ15A(565)
-----------------	-------------------

Reference - Drawing Numbers

Product Specification	PS-10-07
Sales Drawing	SDA-4455

This document was generated on 01/19/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION