

## Toroidal transformer RKE 3000/2x115



### Advantages

Minimum size at high output
Low weight
Double output voltage for series or parallel connection
Minimal no-load losses
Outstanding temperature behaviour thanks to low magnetic leakage field
Very low noise field


### Applications

As a mains transformer for adjustment of the voltage and simple electrical isolation.

As an isolating transformer for the safe electrical isolation of the input and output sides. The transformer may be used to set up protective separation as a protective measure in accordance with VDE 0100.

As a safety isolating transformer for the safe electrical isolation of the input and output sides. The transformer is suitable for creating SELV and PELV circuits because of the limit on the output voltage.

### Circuit Diagram



Parallelschaltung: rot mit grau / schwarz mit orange  
Parallel connection: red with grey / black with orange

Reihenschaltung: schwarz mit grau  
Series connection: black with grey

### Standards



Safety isolating transformer  
to: VDE 0570 Part 2-6, DIN EN 61558-2-6, EN 61558-2-6, IEC 61558-2-6,  
UL 5085-1/-2, CSA 22.2 No.66

### Approvals



UL 5085-1/-2, CSA 22.2 No.66



## Toroidal transformer RKE 3000/2x115

Electrical data	Type	RKE 3000/2x115
	Input	
	Rated input Voltage	230 Vac
	Rated frequency	50 - 60 Hz
	Output	
	Rated output voltage	2 x 115 Vac
	Rated Power	3000 VA
	No-load voltage (app. x factor)	1.01
	No-load loss (typ.)	12.70 W
	Efficiency	98 %
	Standards	
	Classification	Safety isolating transformer
	Approvals	
	Approvals	cURus
	Environment	
	Ambient temperature max.	40 °C
	Safety and protection	
	Type	open type
	Short circuit strength	non-short-circuit proof
	Class of Insulation System	VDE=B, UL=class 105
	Protection index	IP 00
	Safety class (prepared)	II
	Test voltage	4000 Vac, 50 Hz
	Order numbers	
	Order Number	RKE 3000/2x115

Mechanical data	Type	RKE 3000/2x115
	Terminal and mounting	
	Fixing method	Mounting kit, M5 bolt
	Terminals	Connecting leads, 200 mm
	Measures and weights	
	Major diameter Ø	215 mm
	Outside diameter in the area of the wire lead	225 mm
	Height without mounting	130 mm
	Weight	20.90 kg