

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19160-0012](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** Closed-End Insulated Splice for 14-22 AWG Wire, Clear

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification PK-19408-109 \(PDF\)](#)  
[Product Specification PS-19902-013 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Splices  
 Series [19160](#)  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 MolexKits Yes  
 Overview [Splices](#)  
 Product Name Closed-End Insulated  
 UPC 800753110229

**Physical**

Barrel Type Closed  
 Color - Resin Natural  
 Flammability 94V-2  
 Insulation Nylon (PA)  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 0.472/g  
 Packaging Type Bag  
 Temperature Range - Operating 105°C  
 Wire Insulation Diameter 6.10mm max.  
 Wire Size AWG 14, 16, 18, 20, 22

**Electrical**


Voltage - Maximum 300V

**Material Info**

Old Part Number NC-2214

**Reference - Drawing Numbers**

[Packaging Specification](#) PK-19408-109  
[Product Specification](#) PS-19902-013  
[Sales Drawing](#) SD-19160-001



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

19160Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool	<a href="#">0640010600</a>
Crimp Head for the AT-200™ Pneumatic Hand Tool, Crimp from Top	<a href="#">0640053400</a>
Crimp Head for the AT-200™ Pneumatic Hand Tool	<a href="#">0640050600</a>