### PEL 230/12-2



## Advantages

Stabilised and adjustable output voltage

DC OK signalling via LEDs

Parallel connection option

Service-friendly spring-loaded connector system

Panel installation on mounting rails

## **Applications**

Primary switch mode power supply is concentrated on the core task of voltage and current supply. Flat step profile optimized for installation in control panels in the building automation.

### Standards

Primary switched mode power supply to UL 60950, UL 508

EN 61558-2-16, EN 60950-1

EMC: EN 61204-3 **Approvals** 







UL/CSA 60950 recognised, UL508 listed, Germanischer Lloyd





# Single phase, primary switched mode power supply **PEL 230/12-2**

Input rated current (rated load)  Rated frequency range  Starting current limiter  100   1	c (120 - 373 Vdc) 110 / 230 Vac) 7 O Hz
Input voltage range 85 - 264 Va Input rated current (rated load) 0.7 / 0.4 Al Rated frequency range 44 - 66 Hz / Starting current limiter 30 A, NTC Input fuse internal 2 A (slow-bl Recommended back-up fuse (circuit breaker) 6 A, 10 A, 1 Mains buffering 10 / 80 ms Transient surge voltage protection Varistor	c (120 - 373 Vdc) 110 / 230 Vac) ' O Hz ow)
Input voltage range 85 - 264 Va Input rated current (rated load) 0.7 / 0.4 Al Rated frequency range 44 - 66 Hz / Starting current limiter 30 A, NTC Input fuse internal 2 A (slow-bl Recommended back-up fuse (circuit breaker) 6 A, 10 A, 1 Mains buffering 10 / 80 ms Transient surge voltage protection Varistor	110 / 230 Vac) ' O Hz ow)
Transient surge voltage protection variator	O Hz
Transient surge voltage protection variator	ow)
Transient surge voltage protection variator	•
Transient surge voltage protection variator	•
Transient surge voltage protection variator	6 A, characteristics B, C
Transient surge voltage protection variator	
Transient surge voltage protection variator	
Output	
Output rated voltage 12 Vdc ±2 9	б
Output voltage range 10.5 - 15.5	/dc
Output rated current 2.00 A	
Resistance to reverse feed max. 25 Vdc	
Overload behaviour Constant cu	rrent
Ripple factor typ. 100 mV	SS
Parallel connection Yes	
Serial operation Yes	
Efficiency typ. 80 %	
Signaling	
Power Good (DC OK) LED green	
Standards	
Classification Primary swi	ched mode power supply
Approvals	
Approvals cURus, cULu	is, GL
Environment	
Ambient temperature -25° C to +5	5° C
Storage temperature -25° C to +8	15° C
Derating $-3 \%/K > +$	45° C
Current capacity by any mounting position max. 1.4 A	
Safety and protection	
Protection index IP 20	
Safety class II, (in closed	cabinet)
Order numbers	
Order Number PEL 230/12	



