



SLEEVE IT LIMITED

XGR

Sleeve It XGR is based on a unique glass braid construction that permits up to 300% expansion of the internal bore. Sleeve It XGR is constructed from braided E glass yarn with a tough hard resin to impart increased abrasion resistance.

Features

- Resistance to abrasion
- Range 2 - 50mm
- Operational temperature -20°C to 220°C
- Maximum temperature 450°C
- 500v electrical strength (@ 20°C not expanded)
- Hot splash resistant
- Available in black or natural

Sizes Available

Reference	Nominal Relaxed Bore	Maximum Expanded Bore
No.1	20.0mm	50.0mm
No.2	15.0mm	38.0mm
No.3	10.0mm	30.0mm
No.4	8.0mm	25.0mm
No.5	6.0mm	18.0mm
No.6	3.0mm	9.0mm
No.7	2.0mm	6.0mm



All information shown, including illustrations is believed to be reliable. Users, however, should independently evaluate the suitability of the product for their application. Sleeve It makes no warranties as to the accuracy or completeness of the information and disclaims any liability regarding its use. In no case will Sleeve It be liable for any incidental, indirect or consequential damages arising from the sale, resale, use or misuse of the product. Sleeve It specifications are subject to change without notice. In addition Sleeve It reserves the right to make changes in materials and processing, without notification to the buyer, which do affect compliance with any applicable specification.