

UNIVERSAL ENCLOSURES

2000 EMC


A range of high frequency EMC compliant enclosures for shielding electronic equipment.

- Lid and Base moulded in ABS
- Graphite dark grey paint finish
- Electromagnetic compatibility EMC coating
- Lid mounted by four M3 machine screws
- Brass inserts in base for repeated removal of the lid
- Excellent properties for machining
- Integral mounting guides to accept 1.6mm PCB's
- PCB Adaptors (included) for horizontal PCB mounting



| SPECIFICATION | |
|------------------------|--|
| Materials | Lid and base high impact ABS |
| Operating Temperature | Resistant to temperatures of up to 85°C |
| Protection class | IP54 |
| Standard colours | Graphite dark grey |
| Standard unit includes | Base & lid 4x M3 machine screws PCB adaptors |

| GREY | LENGTH | WIDTH | HEIGHT |
|--------------------|--------|-------|--------|
| BIM2008/18-EMI/RFI | 55mm | 55mm | 42mm |
| BIM2000/10-EMI/RFI | 75mm | 50mm | 27mm |
| BIM2001/11-EMI/RFI | 85mm | 56mm | 39mm |
| BIM2002/12-EMI/RFI | 100mm | 50mm | 25mm |
| BIM2003/13-EMI/RFI | 112mm | 62mm | 31mm |
| BIM2007/17-EMI/RFI | 112mm | 62mm | 31mm |
| BIM2004/14-EMI/RFI | 120mm | 65mm | 40mm |
| BIM2030/30-EMI/RFI | 142mm | 80mm | 30mm |
| BIM2005/15-EMI/RFI | 150mm | 80mm | 50mm |
| BIM2006/16-EMI/RFI | 190mm | 110mm | 60mm |
| BIM2009/19-EMI/RFI | 250mm | 200mm | 64mm |



UNIVERSAL
ENCLOSURES

HAND
HELD
CASES

HEAVY
DUTY
ENCLOSURES

DIN
RAIL
BOXES

INTERFACE
SUPPORTS

CONTROL
STATIONS

DIECAST
& METAL
BOXES

DESKTOP &
INSTRUMENT
CASES

POTTING
BOXES

19"
ENCLOSURES

19"
CABINETS

DEVELOPMENT
BOARD
ENCLOSURES

CUSTOM
SIZED
ENCLOSURES

CUSTOM
SERVICES