

For Patient-Care Vicinity - UL1363A Medical-Grade Power Strip with 4 Hospital-Grade Outlets, 15-ft. Cord

MODEL NUMBER: **PS-415-HG-OEM**



Description

Tripp Lite's PS-415-HG-OEM Power Strip is designed to be installed on any mobile cart, diagnostic equipment, instrument, IV pole, etc. It is designed to supply power to plug-connected components of a movable equipment assembly that is rack-, table- or pedestal-mounted. Features 4 output receptacles, 15-ft. AC power cord and two built-in resettable circuit breakers that control power to all outlets and protect against overloads. Switchless design prevents accidental shutoff. Optional-use keyhole mounting tabs and flanges.

PLUG/OUTLETS: NEMA 5-15P-HG hospital-grade plug and 4 NEMA5-15R-HG hospital-grade receptacles

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: All-metal corded multi-outlet strip

Features

- Versatile power distribution strip designed to be installed on any mobile cart, IV pole, etc.
- Meets UL 1363A to supply power to plug-connected components of a movable equipment assembly that is rack-, table- or pedestal-mounted
- 4 x NEMA 5-15R-HG hospital-grade output receptacles
- 15-ft. AC cord with integrated, molded NEMA5-15P-HG hospital-grade plug
- Rugged all-metal housing withstands years of use without breakage
- 15A electrical capacity with two built-in resettable circuit breakers
- 120V, 50/60Hz
- Optional-use keyhole mounting tabs and flanges
- Switchless design prevents accidental shutoff

Specifications

Highlights

- Designed to be installed on any mobile cart, IV pole, etc.
- Tested to UL 1363A to supply power to plug-connected components of a movable equipment assembly that is rack-, table- or pedestal-mounted
- 4 hospital-grade receptacles and hospital-grade plug
- 15-ft. cord
- Two 15-amp resettable circuit breakers

Applications

- Mobile carts, IV poles and other UL 1363A certified usages.
- Can be used in Patient Care Areas, when properly mounted.

Package Includes

- PS-415-HG-OEM Power Strip
- Owner's manual and warranty information



OVERVIEW	
Style	Strip
Model Type	For Patient-Care Areas
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Outlet Orientation	Single row of 4
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Connection Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Input Cord Length (m)	4.572
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	No power switch
PHYSICAL	
Shipping Dimensions (hwd / in.)	15 x 6 x 3.55
Shipping Dimensions (hwd / cm)	38.1 x 15.24 x 9.02
Shipping Weight (lbs.)	3.55
Shipping Weight (kg)	1.61
Unit Dimensions (hwd / in.)	8.65 x 2.5 x 1.5
Unit Dimensions (hwd / cm)	21.97 x 6.35 x 3.81
Unit Weight (lbs.)	2.25
Unit Weight (kg)	1.02
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs and flanges enable mounting to a variety of surfaces
Receptacle Color	White



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color (AC Line Cord)	White
Outlets Measurement (Center to Center)	Inner outlets = 32.5mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
CERTIFICATIONS	
Approvals	TUV tested to UL 1363A
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.