

Coaxial PCB Connector 85_SMA-50-0-144/111_Y

Description

Right angle PCB jack

Interface Standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 18 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0039 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00012705
Catalogue drawing DCA-00012707
Mounting hole DOU-00002524

Ordering Information

Bulk 100 pcs package 85_SMA-50-0-144/111_YH
Single package 85_SMA-50-0-144/111_YE

Remarks

PCB connector with stand-offs