

## Protect It! 6-Outlet Surge Protector, 4-ft. Cord, 790 Joules, Tel/Fax/Modem Protection

MODEL NUMBER: TLP604TEL



### Highlights

- 6 outlets / 4-ft. cord
- 790 joule rating
- Modem/fax surge protection
- \$20,000 Ultimate Lifetime Insurance ((U.S., Canada, and Puerto Rico only)

### Applications

- Ideal for any desktop, network or home computing application requiring AC and dialup or DSL modem line protection.

### Package Includes

- TLP604TEL
- 6-ft. telephone cord
- Instruction manual with warranty information

### Description

Tripp Lite's TLP604TEL Surge Suppressor offers economical AC and phone line surge suppression for full protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. TLP604TEL offers 6 total outlets, 4 foot cord and diagnostic LED to warn of suppressor damage. AC suppression rated at 790 joules shields equipment from surges and line noise. Attractive white suppressor housing with keyhole mounting tabs and 1 designated transformer plug outlet offers convenient protection of desktop computer equipment and accessories. \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/4-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip

SUPPRESSION: AC: 150V RMS Clamping/790 joules/400V UL1449 Let-through

Phone: Single telephone line surge suppression (RJ11 jacks, 2 wire, 1 line)

### Features

- 790 joules AC surge suppression shields equipment from the strongest surges and line noise
- 6 AC outlets with room for 1 transformer plugs without blocking outlets covers computers and peripherals
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ11 jacks, 2 wire, 1 line, includes 6 ft phone cable)
- 4 foot AC line cable
- Built-in power switch and 15 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm surge suppression status
- Attractive white suppressor housing with keyhole mounting tabs allow versatile placement options
- UL1449 3rd Edition Rated (400V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)



## Specifications

OVERVIEW	
Style	Strip
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Transformer Accommodation	Supports 1 large transformer plug accessory without covering remaining outlets, accepts up to 4 transformers total
Outlet Orientation	Single row
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	4
Input Cord Length (m)	1.22
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	35500
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	790
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400V
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes



Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	13.2 x 5.2 x 1.8
Shipping Dimensions (hwd / cm)	33.53 x 13.21 x 4.57
Shipping Weight (lbs.)	.91
Shipping Weight (kg)	0.41
Unit Dimensions (hwd / in.)	10.8 x 1.85 x 1.23
Unit Dimensions (hwd / cm)	27.43 x 4.7 x 3.12
Unit Weight (lbs.)	.82
Unit Weight (kg)	0.37
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Light Gray
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Outlets Measurement (Center to Center)	28.5mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between slots = 101mm; Distance between slot height = 28mm
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 Ultimate Lifetime Insurance
---	--------------------------------------

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.