

150 Watts

- Ultra Slim Design
- 150% Peak Load for 3 seconds
- Ambient Operation from -25 °C to +70 °C
- High Efficiency
- Selectable Overload Characteristic
- Selectable Remote Inhibit or Enable
- 3 Year Warranty



DSA150:

3.92 x 4.92 x 2.18" (99.8 x 125.2 x 55.5 mm)


Models & Ratings

Output Voltage	Output Power	Output Voltage Trim(3)	Output Current	Peak Load ⁽²⁾	Typical Efficiency ⁽¹⁾	Model Number
24 V	150 W	23.52-25.92 V	6.25 A	9.45 A	87%	DSA150PS24
48 V	150 W	47.04-51.84 V	3.125 A	4.8 A	87%	DSA150PS48

Notes

- 1. Typical efficiency at 230 VAC and full load.
- Peak load is for a maximum of 3 s, see Application Notes. Average power is not to exceed nominal output power.
 Output current should be limited so that nominal output power is not exceeded.

Mechanical Details



Pin Connector					
Conn	Pin Designation				
AC	1	Ground			
I/P	2	L			
1/ [3	N			
	1	+Vout			
	2	-Vout			
DC	3	+RC			
O/P	4	-RC			
	5	DC OK			
	6	DC OK			

DSA150 Series

AC-DC Power Supplies



Input					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage - Operating	90		264	VAC	
Input Frequency	47	50/60	63	Hz	
Power Factor		0.9			At 230 VAC. Conforms to EN61000-3-2 Class A
Input Current - Full Load		1.6/0.8		А	115/230 VAC
Inrush Current			33/65	А	At 115/230 VAC
Earth Leakage Current			1.0	mA	At 264 VAC, 60 Hz
Input Protection	T5.0 A / 250 V i	nternal in-line fuse	•	•	

Output						
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Output Voltage - V1	24		48	VDC	See Models and Ratings table	
Initial Set Accuracy			±1	%	At 100% load	
Output Voltage Adjustment			-2/+8	%	See Models and Ratings table	
Minimum Load	0			Α	No minimum load required	
Start Up Delay			1.0	s		
Start Up Rise Time			50	ms		
Hold Up Time	18			ms	At full load and 115 VAC	
Line Regulation			±0.5	%		
Load Regulation			±1	%		
Transient Response - V1			4	%	Recovery within 1% in less than 2 ms for a 50% step load change at 0.2 A/µs	
Ripple & Noise			1	% pk-pk	Measured at 20 MHz bandwidth	
Overvelte se Protection	28		33	V	24 V model	
Overvoltage Protection	56		65	V	48 V model	
Overload Protection				%	See Application Notes	
Short Circuit Protection					Trip & restart (hiccup mode) for 5 cycles then latch. Recycle AC to reset.	
Thermal Protection			95 (±5)	°C	Measured on internal heatsink auto recovery	
Temperature Coefficient			0.03	%/°C		
Remote On/Off	Selectable as Er	Selectable as Enable or Inhibit using front panel switch				

General						
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Efficiency		87		%	See Models & Ratings table	
Isolation: Input to Output	3000			VAC		
Input to Ground	1500			VAC		
Output to Ground	500			VAC		
Switching Frequency		56/75		kHz	PFC/Main converter	
DC OK Signal	Volt free contacts	Volt free contacts rated at 60 VDC/0.3 A, 30 VDC/1.0 A or 30 VAC/0.5 A (resistive load)				
Output LED	Green LED to indicate output on.					
Mean Time Between Failure		>250		kHrs	MIL-HDBK-217F, +25 °C GB	
Weight		1.9 (860)		lb (g)		

DSA150 Series

AC-DC Power Supplies



Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Operating Temperature	-10		+70	°C	See derating curve in Application Notes
Storage Temperature	-40		+85	°C	
Cooling					Natural convection
Operating Humidity	20		95	%RH	Non-condensing
Operating Altitude			3000	m	
Shock					IEC68-2-27, 4 g, 22 ms half sine, 3 times in each of 6 axes
Vibration					IEC68-2-6, 10-500 Hz, 2 g 10 mins/sweep. 60 mins for each of 3 axes

EMC: Emissions

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
Conducted	EN55022	Class B		
Radiated	EN55022	Class B		
Harmonic Current	EN61000-3-2	Class A		
Voltage Fluctuations	EN61000-3-3			

EMC: Immunity


Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
ECD Immunity	EN61000-4-2	6 kV	Δ.	Contact
ESD Immunity	EN01000-4-2	8 kV	Air Discharge	Air Discharge
Radiated Immunity	EN61000-4-3	10 V/m	А	
EFT/Burst	EN61000-4-4	3	A	
Surges	EN61000-4-5	Installation class 3	A	
Conducted	EN61000-4-6	10 V	A	
Magnetic Fields	EN61000-4-8	4	А	
		Dip: 30%, 10 ms	A	
Dips and Interruptions	EN55024	Dip: 60%, 100 ms	A/B	High Line/Low Line
		Dip: 100%, 5000 ms	В	


Safety Approvals


7 11			
Safety Agency	Safety Standard	Notes & Conditions	
UL	UL508	Industrial Control Equipment	
TUV	EN60950-1 A12:2011	Information Technology	
СВ	IEC60950-1 +A1:2009	Information Technology	



Mechanical Details








Pin Connector					
Conn	Pin Designation				
AC	1	Ground			
I/P	2	L			
1/1	3	N			
	1	+Vout			
	2	-Vout			
DC	3	+RC			
O/P	4	-RC			
	5	DC OK			
	6	DC OK			


Notes

- 1. All dimensions in inches (mm)
- 2. Weight: 1.916 lbs (860g)
- 3. Tolerance: ±0.02 in (±0.5 mm)
- 4. Screw terminal: 10-24 AWG cables size.
- 5. Connection screw maximum torque: Input: 4.4lbs-in (0.5 Nm), Output: 7.0 lbs-in (0.79 Nm).


Application Notes

Derating Curves





DC OK




Open = Output fail, if voltage drops below 45% of nominal Closed = Output good

Contact Rating: 0.3 A at 60 VDC, 1.0 A at 30 VDC, 0.5 A at 30 VAC. 500 VDC isolation to output.



Application Notes

Peak Loading




The peak loading and overload characteristics can be programmed into one of two modes by appropriate selection of the OCP mode switch on the front panel.

A peak load of up-to 150% can be taken for a given duration. This duration depends on the percentage of peak load taken and can be determined by graph A below.

If the load is reduced to less than 100% of nominal either before or at the end of the duration, then there is a period of recovery needed to allow the power supply to cool down before the peak load can be re-applied. The time required for recovery depends on the amount of reduction of load and can be determined by graph B below.


However, if the peak load period exceeds the duration indicated by graph A the output will go into constant current mode for protection. The constant current value will be 105% of the nominal rating.


During constant current operation, if the output voltage should fall below 40% of the rated voltage then the output will turn off and try to restart for five times before turning off permanently. Once this has happened, the output will need to be reset by turning the AC mains off and on again.



A peak load of up-to 150% can be taken for a given duration. This duration depends on the percentage of peak load taken as described by graph A.

Once the peak load duration is exceeded, the output will turn off for 3-4 seconds before automatically restarting.





Remote Control

The output can be controlled by applying a voltage between pin 3 of the DC output with respect to pin 4. The effect of the control is dependant upon the RC switch setting on the front panel.

If the switch is set to position 1 then the output can be disabled by applying a suitable voltage.

If the switch is set to position 2 then the output can be enabled by applying a voltage. In the range of $2.5\,\mathrm{V}$ to $9.0\,\mathrm{V}$ limited to $20\,\mathrm{mA}$.

Switch Position	Pin 3 Voltage with respect to Pin 4	Output
1	<0.8 V or Open Circuit	ON
1	>2.5 V, <9.0 V	OFF
2	<0.8 V or Open Circuit	OFF
2	>2.5 V, <9.0 V	ON