

## Protect It! 230V 6-Universal Outlet Surge Protector, 1.8M Cord, British Plug, 750 Joules

MODEL NUMBER: **SUPER6OMNIB**



### Highlights

- 6 universal outlets
- 1.8 m power cord with British plug
- 750 joule rating
- Lighted on/off switch with integrated circuit breaker

### Applications

- Ideal for any desktop, network or home computing application requiring AC surge suppression

### Package Includes

- SUPER6OMNI B AC surge suppressor
- Instruction manual and warranty information

### Description

Tripp Lite's Protect It!™ SUPER6OMNI B offers economical AC surge suppression for full protection of 220-250V workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. The SUPER6OMNI B offers 6 universal outlets and a 1.8 meter AC line cord with a British plug. AC suppression rated at 750 joules shields equipment from surges and line noise. Internal shutters also offer additional protection. Lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Right-angle outlets keep connected cords from blocking adjacent outlets. Attractive light gray high-impact housing.

INPUT: 1.8 m AC line cord with British plug

OUTPUT: 6 universal receptacles

ELECTRICAL: 220-250V AC, 50/60Hz, 10A

FORMAT: Corded multi-outlet strip

SUPPRESSION: - AC: 750 joules

### Features

- Protect It!™ SUPER6OMNI B offers economical AC surge suppression
- 750 joules AC surge suppression shields equipment from surges and line noise
- 6 universal outlets protect computers and peripherals
- Internal shutters provide additional safety
- 1.8 m AC line cord with British plug
- Built-in power switch and 10 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Attractive light gray high-impact housing with keyhole mounting tabs allow versatile placement options
- Right-angle outlets keep connected cords from blocking adjacent outlets

## Specifications



<b>OVERVIEW</b>	
Style	Strip
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) Universal outlets
Circuit Breaker (amps)	10
Overload Protection	10A resettable illuminated combo switch/circuit breaker
Outlet Orientation	right-angled
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Input Connection Type	British
Input Cord Length (ft.)	6
Input Cord Length (m)	1.8
Voltage Compatibility (VAC)	220-250
Maximum Surge Amps	13500
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	Two position power switch
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	750
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	18.50 x 4.50 x 2.00
Shipping Dimensions (hwd / cm)	47.0 x 11.4 x 5.1
Shipping Weight (lbs.)	1.32



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Shipping Weight (kg)	0.60
Unit Dimensions (hwd / in.)	15.50 x 2.50 x 1.25
Unit Dimensions (hwd / cm)	39.4 x 6.4 x 3.2
Unit Weight (lbs.)	1.0
Unit Weight (kg)	0.45
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Yes - slotted
Housing Color	Light Gray
Receptacle Color	Light Gray
Color (AC Line Cord)	light gray
Outlets Measurement (Center to Center)	51mm
Keyhole Slot Mounting Measurement (Center to Center)	219.5mm
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.