

Protect It! 8-Outlet Home Computer Surge Protector, 8-ft. Cord, 1080 Joules, Space-Saving Plug

MODEL NUMBER: **SK6-6**



Highlights

- 8 outlets / 8-ft. cord
- 1080 joule rating
- \$35,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Applications

- Personal computers, CAD/CAM/CAE workstations, network nodes, file servers, point-of-sale terminals, audio/visual devices, and more.

Package Includes

- SK6-6 Surge Suppressor
- Child Safety Covers
- Color-coded cord identifiers
- Warranty information and Instruction manual

Description

The SK6-6 Surge Suppressor from Tripp Lite has 8 outlets and an 8-ft. cord with a space-saving right-angle plug. The unit has 1080 joules of surge energy absorption to handle the strongest surges. Diagnostic LEDs alert the user to potential power problems. \$35,000 Ultimate Lifetime Insurance (USA and Canada Only). The SK6-6 comes with child safety covers and color-coded cord identifiers.

Features

- 8 outlets with child safety covers
- 8-ft. cord with space-saving right-angle plug
- \$35,000 Ultimate Lifetime Insurance (USA and Canada Only) covers connected equipment -
- Surge energy absorption: 1080 joules; 54,500 amps
- 15 amp circuit breaker
- 3 diagnostic LEDs indicate AC present, line fault & protection present
- EMI/RFI noise filtering
- Keyhole supports for wall mounting
- Recessed and lighted power switch
- Color-coded cord identifiers

Specifications

OVERVIEW	
Style	Strip
OUTPUT	



Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Transformer Accommodation	Holds up to 4 large transformer plugs
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P input plug
Input Plug Features	Space-saving right angle plug
Input Cord Length (ft.)	8
Input Cord Length (m)	2.4
Voltage Compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Two position red illuminated on/off power switch
Diagnostic LEDs	PROTECTION PRESENT (green), LINE FAULT (red) and LINE OK (green)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140V
AC Suppression Surge Current Rating	54,500 amps
UL1449 Let Through Rating	400V - UL Verified
Immunity	Conforms to IEE 587 / ANSI C62.41
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (hwd / in.)	1.5 x 2.5 x 13
Unit Dimensions (hwd / cm)	3.8 x 6.4 x 33



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Light Gray
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Outlets Measurement (Center to Center)	28.6mm
Keyhole Slot Mounting Measurement (Center to Center)	114.3mm
SPECIAL FEATURES	
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$35,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.