

1.4kW Single-Phase ATS / Switched PDU, 120V (8 5-15R), 2 5-15P, 100-127V Input, 2 12ft Cords, 1U Rack-Mount

MODEL NUMBER: PDUMH15ATNET



Description

Tripp Lite Switched ATS / Auto Transfer Switch provides a redundant power option for single-corded network devices. Dual input cords support separate connection to PRIMARY and SECONDARY power sources. The ATS will normally maintain continuous output to all outlets as derived from the primary input cable. If the primary power source becomes unstable or fails altogether, the ATS will switch over to the secondary power source until the primary input is restored and stable. Switched PDU features include individually controllable output receptacles and built-in network interface. Super-fast switchover between primary and secondary power sources occurs within milliseconds. ATS functionality is supported by any two compatible AC power sources, regardless of phase angle, to support a variety of advanced redundant power networking applications. Enables fault tolerant hot-swappable UPS protection when used with a single UPS and fully redundant UPS protection when each cord is connected to a separate UPS system. In a two-UPS environment, the primary input cable must be supported by a full time sine wave UPS with zero transfer time. Tripp Lite SmartOnline series is highly recommended for use as the primary UPS in a two-UPS application. ATS configurations utilizing separate mains circuits, backup generators and even separate utility power grid feeds are fully supported. On-board ATS processor constantly evaluates power quality on both input sources to prevent transfer to the secondary source when unavailable or of lower quality than the primary source. Front input LED's display primary or secondary power availability.

Features

- 120V 15A Automatic Transfer Switch (ATS) / Switched PDU (Agency de-rated to 12A continuous)
- Provides a redundant A/B power option for non-redundant networking equipment with a single input power cord
- Switched PDU features enable programmable or real-time power control of individual outlets via built-in network interface
- Digital display continuously reports total output power consumption in amps
- 8 switched NEMA 5-15R outlets
- 1U horizontal rackmount form factor; 14.5 in. / 36.8 cm depth
- Set of two 12 ft. / 3.6m NEMA 5-15P input cables support connection to separate PRIMARY and SECONDARY power sources

Highlights

- Single phase 15A 120V Auto Transfer Switch / ATS PDU
- Enables redundant A/B power option for single-corded network devices
- Separate primary & secondary inputs connect to any two compatible power sources
- 1U horizontal rackmount; 2 NEMA 5-15P inputs; 8 NEMA 5-15R outlets
- Individually switched outlets and Built-in network interface for remote control and monitoring; Two digit visual current meter

Applications

- Auto-Transfer Switch / Switched PDU is ideal for providing switched outlet functionality and redundant A/B power to single-corded network equipment

Package Includes

- ATS / Switched PDU with attached 5-15P input power cord
- Detachable C13 to NEMA 5-15P 12 ft / 3.6m secondary input cord
- Installable 1U mounting brackets
- User manuals with warranty information



- ATS circuits normally maintain output sourced from the primary input cable; As primary input power fails or becomes unstable, the ATS will switch to maintain output sourced from the secondary input cable until power on the primary input is restored and stable
- ATS configurations enable fault-tolerant, hot-swappable UPS protection when used with a single UPS and fully redundant UPS protection when each cord is connected to a separate UPS system (in a two-UPS environment, the primary input cable must be supported by an online UPS with zero transfer time similar to Tripp Lite SmartOnline series)
- Advanced ATS configurations utilizing separate mains circuits, backup generators and even separate out of phase utility power grid feeds are fully supported
- On-board ATS processor constantly evaluates power quality on both inputs to prevent transfer to the secondary source when unavailable or of lower quality than the primary source
- Super-fast switchover between primary and secondary power sources occurs in 2-7 milliseconds
- DHCP/Manual configuration support; Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, SNMPv3, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols
- Compatible with optional ENVIROSENSE temperature monitor
- Outlets are factory programmed for sequential turn-on at 250 millisecond intervals as the PDU is first energized
- Front panel LEDs confirm power availability on both input lines
- TAA Compliant Version Available - Order Tripp Lite PDUMH15ATNETAA

Specifications

OVERVIEW	
Style	Rackmount
PDU Type	Auto-Transfer Switch; Switched
OUTPUT	
Output Capacity Details	1.44kW (120V), 1.52kW (127V), 1.2kW (100V); 15A maximum (Agency de-rated to 12A continuous)
Frequency Compatibility	60 Hz
Output Receptacles	(8) 5-15R
Output Nominal Voltage	100-127V nominal, single phase
Overload Protection	n/a
Outlet Type	NEMA 5-15R
Customized Load Management Receptacles	8 individually controlled outlets
INPUT	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	15A 120V
Maximum Input Amps	15
Maximum Input Amps Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P



Input Cord Length (ft.)	12
Input Cord Length (m)	3.66
Input Cord Details	Set of two input power cables support connection to separate PRIMARY and SECONDARY power sources
Input Phase	Single-Phase
LEDS ALARMS & SWITCHES	
Front Panel LCD Display	Two digit current meter reports whole PDU output load in amps
Front Panel LEDs	8 front panel LEDs display power on / off status for each outlet, plus 2 additional LEDs to indicate input power status for primary and secondary inputs
PHYSICAL	
Shipping Dimensions (hwd / in.)	5.2 x 20.8 x 23.2
Shipping Dimensions (hwd / cm)	13.2 x 52.8 x 58.9
Shipping Weight (lbs.)	16
Shipping Weight (kg)	7.3
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 14.5
Unit Dimensions (hwd / cm)	4.44 x 44.4 x 36.8
Unit Weight (lbs.)	11
Unit Weight (kg)	5
Material of Construction	Metal
Form Factors Supported	1U rackmount
PDU Form Factor	Horizontal (1U, 2U, etc)
ENVIRONMENTAL	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
COMMUNICATIONS	
SNMP Compatibility	Yes, pre-installed SNMPWEBCARD provides remote monitoring via network interface
SPECIAL FEATURES	
TVSS Grounding	Rear grounding lug
CERTIFICATIONS	
TAA Compliant Option	TAA Compliant Version Available - Order Tripp Lite PDUMH15ATNETAA



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Certifications	Tested to UL 60950-1 (USA), CSA (Canada), Class A (Emissions), NOM (Mexico), RoHS compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.