

Isobar 2-Outlet Surge Protector, Direct Plug-in, 1410 Joules, 3 Diagnostic LEDs, 4-in. Height

MODEL NUMBER: ISOBLOK2-0



Highlights

- 2 outlets/direct plug-in
- 1410 joule rating
- Diagnostic LEDs
- All-metal housing
- \$10,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Applications

- Printers, audio/visual devices, appliances, personal computers, point-of-sale terminals, and more.

Package Includes

- ISOBLOK2-0 Surge Suppressor
- Warranty Information
- Owner's manual

Description

Tripp Lite's Isobar ISOBLOK2-0 Surge Suppressor is ideal for protecting audio/visual devices and printers. This premium direct plug-in surge suppressor features 2 outlets, diagnostic LED, and 1410 joules of energy absorption. An all-metal housing stands up to the toughest environments. \$10,000 Ultimate Lifetime Insurance (USA and Canada Only).

Features

- Tripp Lite's ISOBAR is the world's number one selling premium suppressor series with more than 14 million satisfied customers and a safety-tested history of 20+ years.
- 2 outlets with a direct plug-in design
- Surge energy absorption: 1410 joules/48,000 amps
- Diagnostic LEDs indicate "protection present" (green), "grounded" (red) and "line ok" (green)
- EMI/RFI noise filtering
- All-metal housing
- \$10,000 Ultimate Lifetime Insurance (USA and Canada Only) covers connected equipment

Specifications

OVERVIEW	
Style	Direct Plug-In
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Circuit Breaker (amps)	15



INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P input plug
Input Cord Length (ft.)	0
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Diagnostic LEDs	PROTECTION PRESENT (green), LINE FAULT (red) and LINE OK (green)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1410
AC Suppression Response Time	NM = 0 ns. CM = <1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140
AC Suppression Surge Current Rating	48,000 amps
AC Suppression Components Used	Metal oxide varistors, toroidal balanced chokes and VHF capacitors
Safe Thermal Fusing	Prevents unsafe conditions during extreme extended overvoltages and catastrophic occurrences
UL1449 Let Through Rating	330V
EMI / RFI Filtering	40-80 dB
Immunity	Conforms to IEE 587 / ANSI C62.41
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (hwd / in.)	4 x 2.5 x 2.5
Unit Dimensions (hwd / cm)	10.2 x 6.4 x 6.4
Material of Construction	Metal
Housing Color	Light Gray
Receptacle Color	Black
Form Factors Supported	Direct plug-in format with retaining bracket supports wall mounting directly to a standard AC wall socket



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	Tested to UL1449 3rd Edition by ETL
cUL / CSA (Canada)	Approved for Canada by ETL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.