

SmartPro 120V 700VA 450W Line-Interactive Sine Wave UPS, Dual Voltage, Extended Run, SNMP, Webcard, Tower, USB, DB9 Serial

MODEL NUMBER: **SMART700DV**



Highlights

- 700VA tower line interactive UPS
- Maintains 120V output with 120V or 230V input
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule
- USB port, DB9 serial, EPO, Enhanced runtime version
- C14 inlet with NEMA 5-15P cable and 6 5-15R outlets

Package Includes

- SMART700DV UPS System
- Detachable NEMA5-15P power cord
- USB cabling and DB9 serial cabling
- Manual with warranty information

Description

Tripp Lite's dual-voltage SMART700DV line-interactive UPS system maintains 120V nominal output when fed with North American 120V or international 230V input voltage. Protects servers, networking accessories and telecommunications equipment from blackouts, voltage fluctuations and transient surges. Large internal batteries offer 54.5 min. half-load runtime and 22.2 min. full load runtime during power failures. 700VA/450W power handling capability supports a variety of networking, telecom and other applications, including multiple network workstations. Includes 6 UPS-supported outlets. Supports remote monitoring of UPS and site power conditions via built-in USB and RS-232 enabled DB9 ports. Works with PowerAlert UPS monitoring and unattended shutdown software available via free download from www.tripplite.com. Includes complete USB and serial cabling. Built-in audible alarm and 5 front panel LEDs indicate status of line power, battery power, battery low/replace, voltage regulation and load level. Network-grade AC surge suppression protects equipment from damage and performance problems resulting from transient surges.

Features

- Tripp Lite's dual-voltage SMART700DV line-interactive UPS system maintains 120V nominal output when fed with North American 120V or international 230V input voltage
- Includes detachable input cord with NEMA 5-15P input plug
- Built-in C14 inlet supports a variety of user-supplied international high- and low-voltage input cables
- Protects servers, networking accessories and telecommunications equipment from blackouts, voltage fluctuations and transient surges
- Large internal batteries offer 54.5 min. half-load runtime and 22.2 min. full load runtime during power failures
- 700VA/450W power handling capability supports a variety of networking, telecom and various other applications types, including multiple network workstations
- Includes 6 UPS-supported outlets
- Supports remote monitoring of UPS and site power conditions via built-in USB and RS-232 enabled DB9 ports
- Works with PowerAlert UPS monitoring and unattended shutdown software, available via free download from www.tripplite.com
- Includes complete USB and serial cabling
- Built-in audible alarm and 5 front panel LEDs indicate status of line power, battery power, battery low/replace, voltage regulation and load level
- Network-grade AC surge suppression protects equipment from damage and performance problems resulting from transient surges



- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

| OUTPUT | |
|--|--|
| Output Volt Amp Capacity (VA) | 700 |
| Output Watt Capacity (Watts) | 450 |
| Power Factor | 0.6 |
| Nominal Output Voltage(s) Supported | 120V |
| Frequency Compatibility | 50 / 60 Hz |
| Output Voltage Regulation (Line Mode) | -21%, +8% |
| Output Voltage Regulation (Battery Mode) | +/- 5% |
| Output Receptacles | (6) 5-15R |
| Output AC Waveform (AC Mode) | Sine wave |
| Output AC Waveform (Battery Mode) | Pure Sine wave |
| INPUT | |
| Rated input current (Maximum Load) | 4.8A (120V), 2.6A (230V) |
| Nominal Input Voltage(s) Supported | 120V AC |
| UPS Input Connection Type | 5-15P; C14 inlet |
| UPS Input Connection Description | Detachable 120v 5-15P input cable included |
| Input Circuit Breakers | 6A |
| UPS Input Cord Length (ft.) | 6 |
| UPS Input Cord Length (m) | 1.8 |
| Input Phase | Single-Phase |
| BATTERY | |
| Full Load Runtime (min.) | 22.2 min. (450w) |
| Half Load Runtime (min.) | 54.5 min. (225w) |
| DC System Voltage (VDC) | 24 |
| Battery Recharge Rate (Included Batteries) | Less than 4 hours from 10% to 90% (typical, full load discharge) |
| Internal UPS Replacement Battery Cartridge | RBC54 |
| Battery Access | Battery access door |



| | |
|--|--|
| Battery Replacement Description | Hot-swappable, user replaceable batteries |
| VOLTAGE REGULATION | |
| Voltage Regulation Description | Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 147 (120V), 159 to 282 (230V) |
| Overvoltage Correction | A voltage reduction of 12% applies when input voltage is between 125 and 147 (120V), 240 to 282 (230V) |
| Undervoltage Correction | A voltage boost of 14% applies when input voltage is between 83 and 104 (120V), 159V and 199V (230V) |
| LEDS ALARMS & SWITCHES | |
| LED Indicators | 5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status |
| Audible Alarm | Audible alarm indicates power-failure and low-battery conditions |
| Alarm Cancel Operation | Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status |
| Switches | 2 Switches control off/on power status and alarm-cancel/self-test operation |
| SURGE / NOISE SUPPRESSION | |
| UPS AC Suppression Joule Rating | 570 |
| UPS AC Suppression Response Time | Instantaneous |
| EMI / RFI AC Noise Suppression | Yes |
| PHYSICAL | |
| Primary Form Factor | Tower |
| UPS Power Module Dimensions (hwd, in.) | 10.2 x 9 x 12.5 |
| UPS Power Module Dimensions (hwd, cm) | 26 x 22.9 x 31.8 |
| UPS Power Module Weight (lbs.) | 62 |
| UPS Power Module Weight (kg) | 28.1 |
| UPS Shipping Dimensions (hwd / in.) | 15.2 x 17.8 x 14.2 |
| UPS Shipping Dimensions (hwd / cm) | 38.7 x 45.1 x 36.2 |
| Shipping Weight (lbs.) | 65 |
| Shipping Weight (kg) | 29.5 |
| Cooling Method | Fan |
| UPS Housing Material | Steel |
| ENVIRONMENTAL | |
| Operating Temperature Range | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius. |



| | |
|--|--|
| Storage Temperature Range | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius. |
| Relative Humidity | 0 to 95%, non-condensing |
| AC Mode BTU / Hr. (Full Load) | 97.7 |
| Battery Mode BTU / Hr. (Full Load) | 313.4 |
| AC Mode Efficiency Rating (100% Load) | 94% |
| COMMUNICATIONS | |
| Communications Interface | USB (HID enabled); DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface |
| Network Monitoring Port Description | Supports detailed monitoring of UPS and site power conditions |
| LINE / BATTERY TRANSFER | |
| Transfer Time | 2-4 milliseconds |
| Low Voltage Transfer to Battery Power (Setpoint) | 83 (120v), 159 (230v) |
| High Voltage Transfer to Battery Power (Setpoint) | 147 (120v), 282 (230v) |
| SPECIAL FEATURES | |
| High Availability UPS Features | Hot swappable batteries |
| CERTIFICATIONS | |
| UPS Certifications | Tested to UL1778 (USA); Tested to CSA (Canada); CE; Meets FCC Part 15 Category A (EMI) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$250,000 Ultimate Lifetime Insurance |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.