

SmartPro 120V 1.5kVA 1440W Line-Interactive Sine Wave UPS, Extended Run, SNMP, Webcard, 2U Rack/Tower, USB, DB9 Serial

MODEL NUMBER: **SMART1500CRMXL**



Description

Tripp Lite's SmartPro Compact Rackmount Uninterruptible Power Supply (UPS) offers line interactive voltage regulation, network grade surge suppression and long lasting battery support for critical network hardware during blackouts and extended power failures. Larger internal batteries and higher rated wattage makes these systems ideal for network and telecom wiring closets and other limited-space installations. Runtime is expandable with optional BP48V48RT4U and BP48V24-2U reduced-depth external battery packs.

SMART1500CRMXL 2U rackmount 1500VA/1440 watt UPS offers battery-derived sine wave AC output during power failures and extreme voltage variations. Line interactive Automatic Voltage Regulation (AVR) provides two levels of voltage boost during brownouts and one level of voltage cut during overvoltage conditions to maintain regulated 120V nominal output over an input range of 83-145V. Includes NEMA 5-15P input plug and NEMA 5-15R output receptacles. Network management interfaces support simultaneous communications via USB port, DB9 serial port and optional SNMP/Web management accessory card slot. Optional SNMPWEBCARD offers remote management and control of the UPS via direct network connection. Additional ENVIROSENSE accessory, when used in conjunction with SNMPWEBCARD reports temperature, humidity and status of up to two directly connected contact closure sensors. HID-compliant USB interface enables full integration with built-in power management and auto shutdown features of Windows and Mac OS X. Supports detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces at once. Includes PowerAlert monitoring software with USB and serial cables. Emergency Power Off (EPO) interface. Integrated 3-bank programmable PDU switching supports load shedding and remote-reboot of up to 3 individual connected devices. 3-stage metered current monitoring and battery charge status LEDs. Utility power and voltage regulation LEDs. Audible alarm. Self-test. 4-post rackmount accessories included; 2-9USTAND tower stands and 2POSTRMKITWM 2 post rackmount kit available. Field-replaceable, hot-swappable internal batteries and external battery packs. Attractive all-black color scheme.

Features

- Tripp Lite's SmartPro Compact Rackmount Uninterruptible Power Supply (UPS) offers line interactive voltage regulation, network grade surge suppression and long lasting battery support for critical network hardware during blackouts and extended power failures

Highlights

- 1.5kVA / 1500VA / 1440W line interactive 2U rack/tower UPS, Sine Wave
- 120V output, Corrects brownouts and overvoltages from 83V to 145V
- 0.96 Power Factor, Front panel status LEDs
- Extended runtime options up to 1440W
- 4 post compatible mounting accessories
- 97% line-mode efficiency, 3 switched load banks
- USB, RS232, EPO and slot for SNMPWEBCARD option
- 120V NEMA 5-15P input, 8 NEMA 5-15R outlets

Applications

- Distributed Server Rooms
- Network Closets
- Small Business Networks
- Voice over IP (VoIP) Phone Systems

Package Includes

- SmartPro compact rackmount UPS System
- 4-post rackmount installation hardware
- USB and serial cabling



- Larger internal batteries and higher rated wattage make these systems ideal for network and telecom wiring closets and other limited-space installations
- Runtime is expandable with optional BP48V24-2U (limit 1), BP48V60RT-3U (multi-pack compatible) and BP48V27-2US (multi-pack compatible) external battery packs
- Some external battery configurations require the use of Tripp Lite's External Battery Configuration Software (see manual)
- SMART1500CRMXL 2U rackmount 1500VA / 1440 watt UPS offers battery-derived sine wave AC output during power failures and extreme voltage variations
- Line interactive Automatic Voltage Regulation (AVR) provides two levels of voltage boost during brownouts and one level of voltage cut during overvoltage conditions to maintain regulated 120V nominal output over an input range of 83-145V
- Includes NEMA 5-15P input plug and NEMA 5-15R output receptacles
- Network management interfaces support simultaneous communications via USB port, DB9 serial port and optional SNMP/Web management accessory card slot
- Optional SNMPWEBCARD offers remote management and control of the UPS via direct network connection
- Additional ENVIROSENSE accessory, when used in conjunction with SNMPWEBCARD reports temperature, humidity and status of up to two directly connected contact closure sensors
- HID-compliant USB interface enables full integration with built-in power management and auto shutdown features of Windows and Mac OS X
- 97% efficiency in line power mode offers substantially lower operating costs than lower efficiency UPS types
- Supports detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces at once
- Includes PowerAlert monitoring software with USB and serial cables
- Emergency Power Off (EPO) interface
- Integrated 3-bank programmable PDU switching supports load shedding and remote-reboot of up to 3 individual connected devices
- 3-stage metered current monitoring and battery charge status LEDs; Utility power and voltage regulation LEDs; Audible alarm; Self-test
- 4-post rackmount accessories included; 2-9USTAND tower stands and 2POSTRMKITWM 2-post rackmount kit available
- Field-replaceable, hot-swappable internal batteries and external battery packs
- Attractive all-black color scheme

Specifications

| OUTPUT | |
|--|-----------|
| Output Volt Amp Capacity (VA) | 1500 |
| Output kVA Capacity (kVA) | 1.5 |
| Output Watt Capacity (Watts) | 1440 |
| Output kW Capacity (kW) | 1.4 |
| Power Factor | 1 |
| Nominal Output Voltage(s) Supported | 120V |
| Frequency Compatibility | 60 Hz |
| Output Voltage Regulation (Line Mode) | -14%, +8% |
| Output Voltage Regulation (Battery Mode) | +/- 5% |
| Output Receptacles | (8) 5-15R |



| | |
|--|---|
| Load Management Receptacles | Three switchable single-outlet 5-15R load banks |
| Output AC Waveform (AC Mode) | Sine wave |
| Output AC Waveform (Battery Mode) | Pure Sine wave |
| INPUT | |
| Rated input current (Maximum Load) | 12A |
| Nominal Input Voltage(s) Supported | 120V AC |
| UPS Input Connection Type | 5-15P |
| Input Circuit Breakers | 15A |
| UPS Input Cord Length (ft.) | 10 |
| UPS Input Cord Length (m) | 3 |
| Recommended Electrical Service | 15A 120V |
| Input Phase | Single-Phase |
| BATTERY | |
| Full Load Runtime (min.) | 6 min. (1440w) |
| Half Load Runtime (min.) | 14 min. (720w) |
| Expandable Battery Runtime | Extended runtime supported via optional external battery packs |
| External Battery Pack Compatibility | BP48V24-2U (limit 1); BP48V60RT-3U (multi-pack compatible); BP48V27-2US (multi-pack compatible) |
| DC System Voltage (VDC) | 48 |
| Battery Recharge Rate (Included Batteries) | Less than 3 hours from 10% to 90% (typical, full load discharge) |
| Internal UPS Replacement Battery Cartridge | RBC94-2U |
| Battery Access | Front panel battery access door |
| Battery Replacement Description | Hot-swappable, user replaceable batteries |
| VOLTAGE REGULATION | |
| Voltage Regulation Description | Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 145 |
| Overvoltage Correction | Input voltages between 127 and 145 are reduced by 12% |
| Undervoltage Correction | Input voltages between 96 and 108 are boosted by 12% |
| Severe Undervoltage Correction | Input voltages between 83 and 95 are boosted by 24% |
| LEDS ALARMS & SWITCHES | |
| LED Indicators | 5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status |
| Audible Alarm | Audible alarm indicates power-failure, overload and low-battery conditions |
| Alarm Cancel Operation | Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status |



| | |
|---|--|
| Switches | 2 Switches control off/on power status and alarm-cancel/self-test operation; rear panel protected switches support nominal voltage selection |
| SURGE / NOISE SUPPRESSION | |
| UPS AC Suppression Joule Rating | 570 |
| UPS AC Suppression Response Time | Instantaneous |
| EMI / RFI AC Noise Suppression | Yes |
| PHYSICAL | |
| Included Mounting Accessory Description | 4 post rackmount installation accessories included |
| Installation Form Factors Supported with Optional Accessories | 2 post rackmount (2POSTRMKITWM); Wallmount (2POSTRMKITWM); Tower (2-9USTAND) |
| Primary Form Factor | Rackmount |
| UPS Power Module Dimensions (hwd, in.) | 3.5 x 17.5 x 19 |
| UPS Power Module Dimensions (hwd, cm) | 8.9 x 44.4 x 48.3 |
| Rack Height (U Spaces) | 2 |
| UPS Power Module Weight (lbs.) | 60 |
| UPS Power Module Weight (kg) | 27.2 |
| UPS Shipping Dimensions (hwd / in.) | 9.2 x 24 x 20 |
| UPS Shipping Dimensions (hwd / cm) | 23.5 x 61 x 50.8 |
| Shipping Weight (lbs.) | 70.7 |
| Shipping Weight (kg) | 32.1 |
| Cooling Method | Fan |
| UPS Housing Material | Steel |
| ENVIRONMENTAL | |
| Operating Temperature Range | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius |
| Storage Temperature Range | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius |
| Relative Humidity | 0 to 95%, non-condensing |
| AC Mode BTU / Hr. (Full Load) | 151.4 |
| Battery Mode BTU / Hr. (Full Load) | 544 |
| AC Mode Efficiency Rating (100% Load) | 97% |
| COMMUNICATIONS | |



| | |
|--|--|
| Communications Interface | USB (HID enabled); DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface |
| Network Monitoring Port Description | Supports detailed monitoring of UPS and site power conditions |
| PowerAlert Software | Included |
| Communications Cable | USB and DB9 cabling included |
| WatchDog Compatibility | Supports Watchdog application, OS and hard-reboot restart options for remote applications |
| LINE / BATTERY TRANSFER | |
| Transfer Time | 5.5 milliseconds |
| Low Voltage Transfer to Battery Power (Setpoint) | 83 |
| High Voltage Transfer to Battery Power (Setpoint) | 145 |
| SPECIAL FEATURES | |
| High Availability UPS Features | Hot swappable batteries |
| Green Energy-Saving Features | Greater than 95% efficiency - GREEN UPS; Individually controllable load banks |
| CERTIFICATIONS | |
| UPS Certifications | Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty. |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$250,000 Ultimate Lifetime Insurance |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.