

## Datashield In-Line Surge Protector for Network and Digital/Leased Lines, T-1, ISDN, 1-Set RJ11/45/48

MODEL NUMBER: DSUT1CSU



### Description

Tripp Lite's DSUT1CSU offers complete surge suppression for equipment on digital and leased lines, T1 and ISDN interfaces. Ideal for the protection of sensitive "U" and "S/T" interfaces on modems, NT1 devices, CSU/DSUs, terminal adapters and other pieces of high-speed equipment. Convenient 8 position input/output RJ style jacks are RJ11/45/48 compatible, includes 5 inch ethernet patch cable for convenient placement at the protected device network connection. Surge suppression is handled with balanced arrays of high-speed avalanche diodes that divert excess energies created by electrostatic discharges, faulty wiring or lightning away from network interface connections. Tripp Lite network surge suppressors reduce blown interface ports, garbled network transmissions, system lock-ups and hard equipment failure by safely shunting dataline surges to ground.

SUPPRESSION: 1 set RJ11/45/48 in/out jacks, protects wires 1-8, 60V clamping

### Features

- DSUT1CSU offers full surge suppression for CSU/DSU's and other high speed equipment on digital and leased lines, T1 and ISDN interfaces
- Convenient RJ45 input and output connections make for simple installation (RJ45 input/output connections, pins 1-8, 60V clamping)
- 5 inch ethernet patch cable enables ideal protection placed as close as possible to the point of use
- Surge suppression utilizing high speed avalanche diodes divert excess energies on the network to ground

## Specifications

OVERVIEW	
Style	Direct Plug-In
OUTPUT	
Circuit Breaker (amps)	200
INPUT	

### Highlights

- Complete T1 and ISDN (RJ11/45/48) surge protection
- Protects against the effects of electrostatic discharge, faulty wiring and lightning

### Applications

- Ideal for the protection of sensitive "U" and "S/T" interfaces on modems, NT1 devices, CSU/DSUs, terminal adapters and other pieces of high-speed equipment

### Package Includes

- DSUT1CSU dataline protector
- 5 inch RJ45 patch cable
- Instruction manual and warranty information



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Recommended Electrical Service	120V, 230V
Input Connection Type	RJ45
Input Cord Length (ft.)	0
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	0
Clamping Voltage (RMS)	60
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	Yes
Additional Dataline Protection	1-8
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.