

## Protect It! Surge Protector with 6 Right Angle Outlets, 15-ft. Cord, 1340 Joules, Tel/Modem Protection

MODEL NUMBER: **TLM626TEL15**



### Highlights

- 6 right-angle outlets / 15 ft. cord
- 1340 joule rating
- Tel/DSL surge protection (1 line)
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

### Applications

- Ideal for personal computers, TV/VCR/DVD, stereos and lamps/lighting

### Package Includes

- TLM626TEL15 surge suppressor
- 6 ft. RJ-11 phone cord
- Instruction manual and warranty information

### Description

Tripp Lite's TLM626TEL15 surge suppressor offers complete AC and Tel/DSL line surge suppression for comprehensive protection of workstations, personal computers, home stereos, televisions, VCRs, DVD players and other sensitive electronics. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ-11 telephone line suppression jacks protect a single dialup modem, DSL modem, fax or phone line. TLM626TEL15 offers 6 right-angle outlets, a 15 foot power cord and diagnostic LEDs to warn of wiring problems and suppressor damage. AC surge suppression rated at 1340 joules shields equipment from surges and line noise. Rugged metal housing with 2 designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories. \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input - 15 ft. AC line cord with NEMA 5-15P plug/Output - 6 NEMA 5-15R right-angle outlets

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA 5-15R wall receptacle)

FORMAT: Metal strip

SUPPRESSION: AC: 150V RMS Clamping/1340 joules/400V UL1449

### Features

- 6 right-angle outlets
- 15 ft. cord
- Built-in RJ-11 jacks prevent surges from damaging your telephone/DSL/modem/fax equipment; 6 ft. telephone cord included
- Surge suppression rating: 1340 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker protects against overload
- Diagnostic LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
- Convenient keyhole slots allow secure mounting on wall or desk
- Can accommodate up to 2 transformers without blocking adjacent outlets
- Rugged metal case provides extra safety and durability
- Illuminated power switch



- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment

## Specifications

OVERVIEW	
Style	Strip
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Overload Protection	15A resettable combo switch / circuit breaker
Transformer Accommodation	Supports 2 large transformers without covering adjacent outlets
Outlet Orientation	Single row of outlets
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	60000
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1340
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400V



EMI / RFI Filtering	Up to 20dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	2.25 x 15 x 6
Shipping Dimensions (hwd / cm)	5.72 x 38.1 x 15.24
Shipping Weight (lbs.)	2.5
Shipping Weight (kg)	1.13
Unit Dimensions (hwd / in.)	1.5 x 12.25 x 2.25
Unit Dimensions (hwd / cm)	3.81 x 31.12 x 5.72
Unit Weight (lbs.)	1.8
Unit Weight (kg)	0.82
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Keyhole slots enable mounting to a variety of surfaces
Housing Color	Light Gray
Receptacle Color	Light Gray
Color (AC Line Cord)	Black
Form Factors Supported	Supports floor / wall / desktop placement
Outlets Measurement (Center to Center)	Distance between standard outlets = 30.40mm; Distance between transformer and standard outlets = 45mm
Keyhole Slot Mounting Measurement (Center to Center)	225mm
<b>CERTIFICATIONS</b>	
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1449 3rd Edition (AC Suppression)	UL1449 3rd EDITION
UL1363 (Power Tap)	UL1363
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.