

SmartOnline 208/120V 5kVA 3.5kW On-Line Double-Conversion UPS, Extended Run, SNMP, Webcard, 7U Rack/Tower, USB, DB9 Serial

MODEL NUMBER: **SU5000RT3U**



Description

Tripp Lite 5kVA Smart Online Rack / Tower UPS. 5000VA online, double-conversion UPS for server, network and telecommunications equipment. Maintains battery-derived AC output during blackouts with active, full-time power conditioning. Fault-tolerant auto-bypass prevents unexpected service interruptions during overload or internal fault conditions. 3U power module, 2U transformer module and 2U battery pack install in 7 rack spaces. Full-time sine wave output within 2% of selectable 208V and simultaneous 120V AC. Corrects brownouts to 156V and overvoltages to 276V. Frequency regulation locks output power to 50/60Hz (+/-0.2%). Expandable runtime with optional rackmount external battery packs. Dual-conversion UPS converts raw input from AC to DC, then back to perfect sine wave AC output with enhanced protection from harmonic distortion, fast electrical impulses and other hard-to-solve power problems not addressed by other UPS types. Highly efficient operation in optional economy mode setting, saving BTU heat output and energy costs. Network-grade AC surge and noise suppression. Network management interfaces include 2 DB9 ports and SNMPWEBCARD slot. Supports simultaneous detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces. Includes PowerAlert monitoring software and complete cabling. Emergency Power Off (EPO) interface. Front panel LEDs and LCD readout with scroll controls support visual monitoring of all major UPS functions. Audible alarm. Self test. 4-post rackmount accessories included; 2-9U STAND and 2-POSTRMTKITHD accessories available. L6-30P plug-in connection; built-in output receptacles include two L6-30R, two L6-20R and twelve 5-15/20R. Power Distribution Unit (PDU) options supported. Field-replaceable, hot-swappable external battery packs.

Features

- True online, double-conversion UPS provides pure, full-time sine wave AC output free of surges, voltage fluctuations and line noise
- 5000VA/3500 watt output power capacity with dual high/low voltage output compatible with 200-240V and 120V applications simultaneously
- 3U power module, 2U transformer module and 2U battery pack installs in any 19 inch rack enclosure using only 7 rack spaces
- Dual conversion UPS actively converts raw input from AC to DC, then back to perfect sine wave AC output with enhanced protection from harmonic distortion, fast electrical impulses and other hard-to-solve power problems not addressed by other UPS types
- Provides perfectly regulated, sine wave output power free of line noise, transient surges and frequency variation for the most efficient operation of critical servers, networking and telecommunications equipment

Highlights

- 5000VA / 5kVA / 3500W on-line double-conversion UPS
- 208/120V 60Hz output, high efficiency economy mode option
- 7U Rack/Tower compatible; Hot-swappable batteries
- RS232 & EPO ports; support for SNMP/WEB card options
- Front panel LEDs with detailed LCD monitoring and control screen
- Expandable runtime with optional external battery packs
- NEMA L6-30P input (3 wire); L6-30R, L6-20R & 5-15/20R outputs

Package Includes

- SU5000RT3UPM UPS Power Module
- BP240V5RT2U Battery Pack
- SU5000XFMRT2U Step-down Transformer
- PowerAlert UPS management software and complete cabling
- 4-post rackmount installation accessories
- Instruction manual

- Accepts input voltages between 156 and 276, regulating output within 2% of 208 - plus 120V nominal voltage
- Supports connected equipment during blackouts for 20/8 minutes at half/full load levels, runtime is further expandable with optional external battery packs
- Network interfaces support simultaneous communications via 2 DB9 ports and SNMPWEBCARD slot
- Included PowerAlert UPS monitoring software supports safe unattended shutdown, monitoring and control via local connected servers, plus any number of additional servers over IP
- Communications ports support on-battery, low-battery, power-restored, AC-voltage, DC-voltage, output current monitoring, battery charge current, battery capacity, AC line frequency, timed inverter shutoff, activate self-test and output power control
- Built-in Emergency Power Off (EPO) interface with cable
- Includes 17 built-in output receptacles (3 L6-30R w/one L6-30R used for transformer connection, 2 L6-20R, 12 NEMA 5-15/20R)
- L6-30P input plug-in connection
- Front panel LEDs and LCD readout with scroll button enables visual confirmation of all major UPS functions and current site electrical conditions
- Front panel switches enable power on/off control, self-test and alarm cancel functions
- Included adjustable mounting rails support installation in 4 post 19 inch rack enclosures, optional 2POSTRMKITHD supports 2 post rackmount installation
- Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions

Specifications

OUTPUT	
Output Capacity Details	Supports up to 102% load continuously in double conversion mode, 102 to 125% for 1 minute, 126% to 150% for 30 seconds; Loads over 150% trigger immediate bypass mode operation to support loads directly from mains power; Double conversion mode is automatically restored as the overload is cleared
Output Volt Amp Capacity (VA)	5000
Output kVA Capacity (kVA)	5
Output Watt Capacity (Watts)	3500
Output kW Capacity (kW)	3.5
Power Factor	0.7
Crest Factor	3:1
Nominal Output Voltage(s) Supported	120V; 208V
Nominal Voltage Details	This configuration requires the Power Module be set to 208V output voltage; Included step-down transformer supports 120V output
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Output frequency matches input nominal on startup
Output Voltage Regulation (Line Mode)	+/- 2%
Output Voltage Regulation (Economy Line Mode)	+/- 10%
Output Voltage Regulation (Battery Mode)	+/- 2%
Output Receptacles	(12) 5-15/20R; (2) L6-20R; (2) L6-30R
Output Circuit Breakers	20A breakers (x4) on transformer module protect 3 5-15/20R outlets each, 20A breaker on power module protects L6-20R outlets, L6-30R outlets are unbreakered



Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
INPUT	
Rated input current (Maximum Load)	24A (208V)
Nominal Input Voltage(s) Supported	208V AC
UPS Input Connection Type	L6-30P
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3
Recommended Electrical Service	30A 208V
Input Phase	Single-Phase
BATTERY	
Full Load Runtime (min.)	8 min. (3500w)
Half Load Runtime (min.)	20 min. (1750w)
Expandable Battery Runtime	Supports extended runtime with optional external battery packs
External Battery Pack Compatibility	BP240V10RT3U; BP240V557C-1PH; BP240V787C-1PH; BP240V1037C-1PH; BP240V1407C-1PH
DC System Voltage (VDC)	240
Battery Recharge Rate (Included Batteries)	Less than 6 hours from 10% to 80% (typical, full load discharge)
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Online, double-conversion power conditioning
Overvoltage Correction	2% output voltage regulation during overvoltages to 276
Undervoltage Correction	2% output voltage regulation during undervoltages to 130
LEDS ALARMS & SWITCHES	
LED Indicators	6 LEDs indicate line power, online mode, economy/bypass mode, on-battery, charger and AC output status; LCD screen offers additional information and control options
Front Panel LCD Display	Selectable LCD display with scroll and selection buttons enables UPS control and detailed monitoring options; LED/LCD panel rotates for viewing in rack/tower formats (see manual)
Audible Alarm	Unique audible alarms for all major UPS, environmental and power conditions (see manual)
Alarm Cancel Operation	Alarm cancel switch
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; 2 additional switches support set and execute scrolling LCD functions
SURGE / NOISE SUPPRESSION	



UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
ISOLATION	
Output Isolation Transformer	120V 5-15/20R outlets include load isolation transformer protection
PHYSICAL	
Included Mounting Accessory Description	3 sets of adjustable 4 post rackmount installation rails included
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITHD); Tower (2-9USTAND)
Optional Mounting Accessory Notes	3 sets of 2POSTRMKITHD required for 2 post rackmount installation of separate power module, transformer and battery pack
Primary Form Factor	Rackmount
UPS Power Module Dimensions (hwd, in.)	5.2 x 17.5 x 26
UPS Power Module Dimensions (hwd, cm)	13.3 x 44.4 x 66
Installed Whole System Maximum Rack Depth (in.)	26
Installed Whole System Maximum Rack Depth (cm)	66
Rack Height (U Spaces)	7
UPS Power Module Weight (lbs.)	42
UPS Power Module Weight (kg)	19.1
UPS Dimensions Details	Includes 3U power module, 2U stepdown transformer and 2U external battery pack
Stepdown Transformer Dimensions (hwd / in.)	3.5 x 17.5 x 21
Stepdown Transformer Dimensions (hwd / cm)	8.9 x 44.4 x 53.3
Stepdown Transformer Weight (lbs.)	57
Stepdown Transformer Weight (kg)	25.9
Included Battery Pack Dimensions (hwd / in.)	3.5 x 17.5 x 22.5
Included Battery Pack Dimensions (hwd / cm)	8.9 x 44.4 x 57.2
Included Battery Pack Weight (lbs.)	92
Included Battery Pack Weight (kg)	41.8
UPS Shipping Dimensions (hwd / in.)	30 x 25 x 33
UPS Shipping Dimensions (hwd / cm)	76.2 x 63.5 x 83.8



Shipping Weight (lbs.)	288
Shipping Weight (kg)	130.8
Cooling Method	Fan
UPS Housing Material	Steel
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	1322.2
AC Economy Mode BTU / Hr. (Full Load)	759.6
AC Mode Efficiency Rating (100% Load)	90%
AC Economy Mode Efficiency Rating (100% Load)	94%
COMMUNICATIONS	
Communications Interface	DB9 Serial; Contact closure; EPO (emergency power off); Slot for SNMP/Web interface
Network Monitoring Port Description	RS232 and contact closure communications are located on two separate DB9 ports
PowerAlert Software	Included
Communications Cable	DB9 cable included
LINE / BATTERY TRANSFER	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode
Low Voltage Transfer to Battery Power (Setpoint)	156
High Voltage Transfer to Battery Power (Setpoint)	276
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Hot swappable batteries
Green Energy-Saving Features	High efficiency economy mode operation; Schedulable daily hours of economy mode operation
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Tested to GOST (Russia); Tested to SASO (Saudi Arabia); Meets FCC Part 15 Category A (EMI)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.