

SmartPro 120V 1.5kVA 980W Line-Interactive UPS, Tower, USB, DB9 Serial

MODEL NUMBER: **SMART1500**



Highlights

- 1.5kVA / 1500VA line interactive tower UPS system
- 120V output, Corrects brownouts and overvoltages from 75V to 147V
- Front panel status LEDs with load and battery capacity level display
- USB & RS232 ports, 1 switched load bank, Hot-swap batteries
- NEMA 5-15P input, 6 5-15R outlets

Package Includes

- SMART1500 UPS System
- USB and DB9 monitoring cables
- PowerAlert unattended shutdown and UPS/Power monitoring software

Description

Tripp Lite's SMART1500 intelligent, line interactive UPS system protects servers, networking accessories and telecommunications equipment from blackouts, voltage fluctuations and transient surges. Large internal batteries offer 20 minutes half load runtime and 7 minutes at full load during power failures. 1500VA/980 watt power handling capability supports a variety of networking, telecom and various other application types, including the support of multiple network workstations. Includes a total of 6 outlets, 1 of which can be individually powered on and off via software interface to selectively reboot remote equipment or to automatically shed less significant loads to extend battery runtime for more critical equipment. Supports remote monitoring of UPS and site power conditions via built-in USB and DB9 monitoring ports. Includes PowerAlert UPS monitoring and unattended shutdown software with complete cabling. Built-in audible alarm and 5 front panel LEDs indicate status of line power, battery power, battery low/replace, voltage regulation and load level. Wall mountable with optional UPSWM wallmount bracket. Network-grade AC surge suppression protects equipment from damage and performance problems resulting from transient surges. Attractive, small-footprint tower housing uses less than 66 square inches of floor or desktop space.

Features

- 1500VA/980 watt power handling capability supports a variety of networking, telecom and various other application types
- Built-in voltage regulation and battery support, plus complete AC suppression prevents equipment damage, data loss and downtime
- Large internal batteries offer 20 minutes half load runtime and 7 minutes at full load during power failures
- Automatic Voltage Regulation (AVR) circuits with two boost and one voltage reduction level maintains usable 120V nominal output over an input voltage range of 75-147V
- Includes a total of 6 NEMA5-15R outlets, 1 of which can be individually powered on and off via software interface to selectively reboot remote equipment or shed less significant loads to extend battery runtime for more critical equipment
- Includes 1 USB and 1 DB9 monitoring port for remote monitoring of UPS status and site power conditions
- Communications ports enable safe unattended shutdown without data loss during extended power failures
- Communications ports support messaging of UPS and line power status, including on-battery, low-battery, power-restored, AC line voltage, DC battery voltage and battery capacity
- Communications ports support timed inverter shutoff after unattended shutdown, activate self-test and 10 second reboot of connected equipment
- PowerAlert UPS monitoring and unattended shutdown software with complete cabling included



- Supports Tripp Lite's WatchDog software application to restore unresponsive programs by automatically restarting them and rebooting completely locked computers by automatically switching UPS power off and back on again
- Notification of system status via 5 LEDs and multi-function audible alarms
- Wall mountable with UPSWM wallmount bracket
- Attractive small footprint beige tower housing uses less than 66 square inches
- Hot-swappable/user replaceable batteries allow on-site battery replacement
- Cold start capability enables UPS turn-on in battery mode during blackout conditions

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	1500
Output kVA Capacity (kVA)	1.5
Output Watt Capacity (Watts)	980
Power Factor	0.7
Nominal Output Voltage(s) Supported	120V
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-18%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(6) 5-15R
Load Management Receptacles	One switchable single-outlet 5-15R load bank
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
INPUT	
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	15A
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
BATTERY	



Full Load Runtime (min.)	7 min. (980w)
Half Load Runtime (min.)	20 min. (490w)
DC System Voltage (VDC)	36
Battery Recharge Rate (Included Batteries)	Less than 4 hours from 10% to 90% (typical, full load discharge)
Internal UPS Replacement Battery Cartridge	RBC36-SLT
Battery Access	Battery access door
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 75 to 147
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 93 and 107 are boosted by 14%
Severe Undervoltage Correction	Input voltages between 75 and 92 are boosted by 30%
LEDS ALARMS & SWITCHES	
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
Audible Alarm	Audible alarm indicates power-failure, overload and low-battery conditions
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	480
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Installation Form Factors Supported with Optional Accessories	Wallmount (UPSWM - tower mounting kit)
Primary Form Factor	Tower
UPS Power Module Dimensions (hwd, in.)	12.8 x 7.5 x 9
UPS Power Module Dimensions (hwd, cm)	32.4 x 19 x 22.9
UPS Power Module Weight (lbs.)	38.4
UPS Power Module Weight (kg)	17.4
UPS Shipping Dimensions (hwd / in.)	18.2 x 12 x 13.8



UPS Shipping Dimensions (hwd / cm)	46.4 x 30.5 x 34.9
Shipping Weight (lbs.)	42.6
Shipping Weight (kg)	19.3
Cooling Method	Fan
UPS Housing Material	PVC
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	138.8
Battery Mode BTU / Hr. (Full Load)	454.4
AC Mode Efficiency Rating (100% Load)	96%
COMMUNICATIONS	
Communications Interface	USB; DB9 Serial
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	Included
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	75
High Voltage Transfer to Battery Power (Setpoint)	147
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.