

## Isobar 12-Outlet Rack-Mount Surge Protector, 15-ft Cord, 3840 Joules, Locking Switch Cover

MODEL NUMBER: ISOBAR12ULTRA



### Description

Tripp Lite's ISOBAR12ULTRA offers network-grade surge and noise suppression in a versatile all-metal multi-mount cabinet. Detachable mounting flanges are configurable for rack mount, wall mount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19 inch EIA standard rack. Features the highest level of AC surge and EMI/RFI noise suppression of all Tripp Lite rackmount surge protectors. Outlets are arranged in exclusive isolated filter banks to limit noise interaction among connected items. Includes 12 outlets (2 front/10 rear), 15 ft AC power cord and guarded power switch to reduce the risk of accidental shutoff. Diagnostic LEDs indicate AC present, line fault and protection status. \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) coverage .

PLUG/OUTLETS: Input: NEMA 5-15P/Output: 12 NEMA5-15R (2 front & 10 rear)

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA 5-15R wall receptacle)

FORMAT: Supports 19 in. rack mount (uses 1 rack space/1U), wall mount, under-counter and more

### Features

- Tripp Lite's ISOBAR is the world's number one selling premium protector series with more than 18 million satisfied customers and a safety-tested history of 20+ years.
- Versatile all-metal cabinet with detachable mounting flanges allows rack mount, wall mount, under-counter and other creative mounting options
- Uses one rack space (1U) in standard 19 inch rack ("zero U" mounting possible in many racks) 3840 joules/96,000 amp network-grade AC surge suppression with EMI/RFI filtering
- 12 NEMA5-15R output receptacles (2 front/10 rear)
- Outlets are arranged in exclusive isolated filter banks to limit noise interaction among connected items
- 15 foot AC cord with NEMA5-15P straight-in plug connection
- Diagnostic LEDs confirm AC present (green), Line Fault (red) and Protected (green)
- Lighted power switch confirms power on/off status

### Highlights

- 12 outlets (2 front, 10 rear)
- Extra-long 15-ft cord
- 3840 joule rating—more joules mean more protection!
- All-metal housing with diagnostic LEDs
- Isolated filter banks remove damaging line noise
- Switch safety cover prevents accidental shutoff

### Applications

- Ideal for the protection of sensitive electronic equipment in 19 inch rackmount, wallmount and under-counter applications, such as internetworking equipment, PC systems, telecommunications, audio/video, security, sound reinforcement and more.

### Package Includes

- ISOBAR12ULTRA Surge Protector
- Warranty information
- Instruction manual



- Snap-in switch guard prevents accidental turn off
- 15 amp capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

OVERVIEW	
Style	Rack-Mount
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(12) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P input plug
Input Plug Features	Space-saving right angle input plug
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Voltage Compatibility (VAC)	120
Maximum Surge Amps	150000
LEDS ALARMS & SWITCHES	
Switches	Red illuminated power switch controls power to all outlets
Diagnostic LEDs	PROTECTION PRESENT (green), LINE FAULT (red) and LINE OK (green)
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3840
AC Suppression Response Time	NM = 0 ns. CM = <1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140
AC Suppression Surge Current Rating	96,000 amps



AC Suppression Components Used	Metal oxide varistors, toroidal balanced chokes and VHF capacitors
Safe Thermal Fusing	Prevents unsafe conditions during extreme extended over-voltages and catastrophic occurrences
UL1449 Let Through Rating	330V
EMI / RFI Filtering	40-80 dB
Immunity	Conforms to IEE 587 / ANSI C62.41
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	2.25 x 20.5 x 9.25
Shipping Dimensions (hwd / cm)	5.72 x 52.07 x 23.50
Shipping Weight (lbs.)	5.7
Shipping Weight (kg)	2.59
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4
Unit Dimensions (hwd / cm)	4.45 x 44.45 x 10.16
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.09
Material of Construction	Metal
Included Mounting Accessories	Included mounting flanges are pre-installed for 1U rackmount installation and can be re-configured to support a variety of mounting options
Housing Color	Black
Receptacle Color	Black
Color (AC Line Cord)	Black
Form Factors Supported	1U rackmount, 0U vertical rackmount, wallmount and under-counter mounting supported - detachable flanges can be re-configured to support a variety of additional mounting options
Outlets Measurement (Center to Center)	Distance between front outlets = 38.9mm; Distance between rear outlets = 38.9mm
<b>SPECIAL FEATURES</b>	
Right-Angle Plug	Yes
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	Tested to UL1449 3rd Edition by ETL
cUL / CSA (Canada)	Approved for Canada by ETL



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.