

## SmartPro 120V 2.2kVA 1.7kW Line-Interactive UPS, Tower, 3-DB9 Serial ports

MODEL NUMBER: **SMART2200NET**



### Description

Tripp Lite's SMART 2200NET intelligent, line interactive large tower UPS system protects servers, networking accessories and telecommunications equipment from blackouts, voltage fluctuations and transient surges. Large internal batteries offer 27 minutes half load runtime and 11 minutes fully loaded. Runtime is expandable with optional BP24V28-2U (limit 1) and BP24V70-3U external battery packs. 2200VA/1700 watt power handling capability supports a variety of networking, telecom and other sensitive electronic applications. Includes 6 protected outlets. Supports remote monitoring of UPS and site power conditions via built-in RS-232 enabled monitoring port, plus standard UPS monitoring via 2 built in contact closure ports. Includes PowerAlert UPS monitoring and unattended shutdown software with complete cabling. Built-in audible alarm and front panel LEDs indicate line power, battery power, battery charge level, load level, plus voltage regulation status. Network grade AC surge suppression protects equipment from damage and performance problems resulting from transient surges.

### Features

- SMART 2200NET line interactive UPS offers battery derived AC output during power outages, voltage regulation during brownouts and overvoltages, plus network-grade AC surge suppression
- 2200VA/1700 watt power handling capability supports a variety of networking, telecom and other sensitive electronic devices
- Large internal batteries offer runtimes of 27 minutes at half load (1100VA/850 watts) and 11 minutes at full load (2200VA/1700 watts)
- Runtime is further expandable with optional external BP24V28-2U (limit 1) and BP24V70-3U (multi-pack compatible) battery packs
- Automatic Voltage Regulation (AVR) circuits maintain 120V nominal output over an input voltage range of 87-140V
- Includes 6 fully protected NEMA 5-15R outlets with 2 single outlet load banks that can be individually powered off and back on again via software interface
- PowerAlert UPS monitoring and unattended shutdown software enables configurable network broadcast messaging, email notification, event logging and running user defined script commands
- Offers simultaneous monitoring of up to 3 directly connected devices through included DB9 contact closure and RS-232 enabled interfaces, or the monitoring of any number of additional servers over IP with included PowerAlert monitoring software
- In addition to the contact closure monitoring of on battery, low battery and power restored messaging, built-in RS-232 interface supports messaging of UPS and line power status, including AC line voltage, DC battery voltage and remaining battery capacity
- Supports activate self-test and UPS output power control for delayed or immediate reboot of connected equipment
- Diagnostic LEDs (indicate 17 performance conditions)

### Highlights

- 2.2kVA / 2200VA line interactive, extended-run tower UPS
- 120V output, Corrects brownouts and overvoltages from 87V to 140V
- 3 DB9 communication ports (1 RS232 / 2 contact-closure)
- Front panel status LEDs with load and battery capacity display
- 2 independently switchable output load banks
- NEMA 5-15P input, 6 NEMA 5-15R outlets

### Package Includes

- SMART 2200NET UPS System
- PowerAlert Software and three 6 foot network cables
- Instruction manual



## Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	2200
Output kVA Capacity (kVA)	2.2
Output Watt Capacity (Watts)	1700
Output kW Capacity (kW)	1.7
Power Factor	0.8
Nominal Output Voltage(s) Supported	120V
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-13% / +5%
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(6) 5-15R
Load Management Receptacles	Two switchable single outlet 5-15R load banks
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
INPUT	
Rated input current (Maximum Load)	15A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	20A
UPS Input Cord Length (ft.)	8
UPS Input Cord Length (m)	2.4
Recommended Electrical Service	20A 120V
Input Cord Length (ft.)	8
Input Cord Length (m)	2.4
Input Phase	Single-Phase
BATTERY	
Full Load Runtime (min.)	11 min. (1700w)
Half Load Runtime (min.)	27 min. (850w)
Expandable Battery Runtime	Extended runtime supported via optional external battery packs



External Battery Pack Compatibility	BP24V28-2U (limit 1); BP24V70-3U (multi-pack compatible)
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	Less than 9 hours from 10% to 90% (typical, full load discharge)
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 87 to 140
Overvoltage Correction	Input voltages between 127 and 140 are reduced by 12%
Undervoltage Correction	Input voltages between 95 and 105 are boosted by 10%
Severe Undervoltage Correction	Input voltages between 87 and 94 are boosted by 22%
<b>LEDS ALARMS &amp; SWITCHES</b>	
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; set of 4 rear-panel switches control system enable and contact closure port inverter shutoff commands
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	720
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Primary Form Factor	Tower
UPS Power Module Dimensions (hwd, in.)	17 x 9 x 12.5
UPS Power Module Dimensions (hwd, cm)	43.2 x 22.9 x 31.8
UPS Power Module Weight (lbs.)	80
UPS Power Module Weight (kg)	36.3
UPS Shipping Dimensions (hwd / in.)	22.2 x 12.8 x 16.5
UPS Shipping Dimensions (hwd / cm)	56.5 x 32.4 x 41.9
Shipping Weight (lbs.)	87
Shipping Weight (kg)	39.5
UPS Housing Material	Polycarbonate



<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	58.4
Battery Mode BTU / Hr. (Full Load)	863.7
AC Mode Efficiency Rating (100% Load)	99%
<b>COMMUNICATIONS</b>	
Communications Interface	DB9 Serial; Contact closure
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions; contact closure communications via two additional DB9 ports (3 total)
PowerAlert Software	Included
Communications Cable	3 DB9 cables included
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	87
High Voltage Transfer to Battery Power (Setpoint)	140
<b>SPECIAL FEATURES</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
Green Energy-Saving Features	Individually controllable load banks
<b>CERTIFICATIONS</b>	
UPS Certifications	Meets FCC Part 15 Category A (EMI); ROHS (Restriction of Hazardous Substances); Tested to CSA (Canada); Tested to NOM (Mexico); Tested to UL1778 (USA)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance