

OSRAM TRUCKSTAR® PRO product range




| Product Reference | ECE | Product Number | V | W | | | | No. |
|-----------------------|--------|----------------|----|-------|-----------|----|-----|--------------------|
| 64155TSP | H1 | 4008321784179 | 24 | 70 | P14.5s | 1 | 100 | 6 ^{P.78} |
| 64155TSP-HCB | H1 | 4008321784209 | 24 | 70 | P14.5s | 2 | 20 | 6 ^{P.78} |
| 64156TSP | H3 | 4008321784261 | 24 | 70 | PK22s | 1 | 100 | 10 ^{P.78} |
| 64156TSP-HCB | H3 | 4008321784292 | 24 | 70 | PK22s | 2 | 20 | 10 ^{P.78} |
| 64196TSP | H4 | 4008321785046 | 24 | 75/70 | P43t | 1 | 100 | 17 ^{P.78} |
| 64196TSP-HCB | H4 | 4008321785077 | 24 | 75/70 | P43t | 2 | 20 | 17 ^{P.78} |
| 64215TSP | H7 | 4008321785114 | 24 | 70 | PX26d | 1 | 100 | 22 ^{P.78} |
| 64215TSP-HCB | H7 | 4008321785145 | 24 | 70 | PX26d | 2 | 20 | 22 ^{P.78} |
| 64216TSP | H11 | 4052899904804 | 24 | 70 | PGJ19-2 | 1 | 100 | 27 ^{P.78} |
| 64216TSP-HCB | H11 | 4052899904644 | 24 | 70 | PGJ19-2 | 2 | 20 | 27 ^{P.78} |
| 7510TSP ²⁾ | PY21W | 4008321798169 | 24 | 21 | BAU15s | 10 | 50 | 54 ^{P.79} |
| 7511TSP | P21W | 4008321798107 | 24 | 21 | BA15s | 10 | 50 | 51 ^{P.79} |
| 7537TSP | P21/5W | 4008321798138 | 24 | 21/5 | BAY15d | 10 | 50 | 52 ^{P.79} |
| 2845TSP | W5W | 4008321798077 | 24 | 5 | W2.1x9.5d | 10 | 50 | 67 ^{P.79} |
| 5627TSP | R5W | 4008321795151 | 24 | 5 | BA15s | 10 | 50 | 63 ^{P.79} |
| 5637TSP | R10W | 4008321795205 | 24 | 10 | BA15s | 10 | 50 | 63 ^{P.79} |
| 3930TSP | T4W | 4008321795106 | 24 | 4 | BA9s | 10 | 50 | 90 ^{P.79} |



Perfect match: Premium 24 V LED Retrofits – a more modern and efficient interior light for trucks

For interior applications, easy to install: brighter light with up to 80 % less energy consumption.
See page 14



1) Compared with standard lamps | 2) Amber lamps for clear indicator lights