

# Speed Controllers - REE



This single phase electronic control device provides a simple solution to speed controlling single or multiple fans. It has a manual dial which can change the fan speed from a minimum setting ( factory set to approx 20%) to 100%.

- 230V 50Hz single phase AC input
- Current rating options - 1, 3, 5 & 7 Amps
- On/Off Switch
- Internal pre-set for minimum speed
- Two wire control - for simple connection
- Three wire control - lower motor running temperature (increased fan life) and improved speed adjustment response.

Part Number	Supply voltage VAC	Frequency Hz	Max Current rating Amps	Ambient Temperature °C	Width mm	Height mm	Depth mm
REE10	230	50	1	40	104	84	40
REE30	230	50	3	40	119	99	41
REE50	230	50	5	40	118	95	57
REE70	230	50	7	40	120	95	73




## Electromagnetic compatibility

These controllers comply with the relevant EC council Directives, EMC Directive 89/336/EEC and amendment 92/31/EEC. Applied harmonised standards EN50081-1 and EN500821.

## Suppression

These controllers incorporate illuminated isolator switch, have radio interference suppression to BS800/1977, CISPR and VDE 0875 (residential applications and installations).

### 2 Wire



### 3 Wire

