

PAR30L

Cat # CGP3025B8D

Performance Parameters		Units	Value			Test Condition Notes
			Min	Spec	Max	
Supply Voltage AC		V	120			Clear and Steady Voltage
Input Power		W	12.5			
Luminous Flux	3000K	lm	–	850	–	
Color Temperature		K	2870	3045	3220	ANSI NEMA ANSLG C78.377
Color Rendering Index (CRI)		Ra	80	–	–	
Beam Angle at 50% I _v (2α)±3°		°	25°			
Energy Star Certified			Yes			
Dimming			Yes			
Base Type			E26			
Input Frequency		Hz	60 Hz			
Input Current		mA	–	110	–	25°C
Power Factor		λ	0.9			
Luminous Efficiency	3000K	lm/W	–	68	–	

Starting and Lifetime			Min	Spec	Max	Test Condition Notes
L ₇₀ Life Time		hrs	–	25000	–	25°C
Start Up Time Without Dimmer		S	–	–	1	Rated Supply Voltage 25°C
Operating Temperature Range		°C	-20	25	45	

Safety Characteristics

Withstand High Voltage Test	V	1240			
-----------------------------	---	------	--	--	--

Certification: UL, FCC

Standard: UL1993, UL8750, Part15

Damp locations only. Do not use where directly exposed to water. Not for use in totally enclosed luminaires.

PAR30L

Cat # CGP3025B8D



Catalog #	CGP3025B8D
Description	PAR30L 3000K, 25°, Dimmable
Stock Number	70-0800-3027-6
Billing Unit	EA
Qty/Case	8
MOQ	1 Case
Item UPC	000-51128-94418-9
Case UPC	500-51128-94418-4
Case Dimension L × W × H	17.165" × 9.125" × 6.72"
Case Weight (lbs)	6.458
Case Cube (cu. ft.)	0.609

LIMITED WARRANTY: Warranted to last 3 years based on 3 hours normal use per day at 120 V. 3M makes no other warranties, express or implied, including any warranty of merchantability or fitness for a particular purpose. At 3M's option, refund or replacement is the sole remedy. This Limited Warranty does not cover accident, neglect, abuse, misuse or acts of God. LIABILITY FOR DIRECT, INDIRECT, INCIDENTAL OR CONSEQUENTIAL DAMAGES IS EXPRESSLY EXCLUDED, except where prohibited by law. For warranty claims and additional details, please visit 3MLighting.com/LED.



3M Company
3M Center
St. Paul, MN 55144-1000
1.800.430.5000
3MLighting.com/LED

3M is a trademark of 3M. Used under license in Canada. All other trademarks herein are property of their respective owners. Please recycle.
Printed in USA. ©3M 2014. All rights reserved.
HB10118 11012014 98-0004-1014-6