

Productname : Acrylic Paint
Ref.Nr.: BDS000794_3_20140625 (EN)
Creationdate : 25.06.14 Version : 2.0
Replaces: BDS000794_20120614

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Acrylic Paint
all solid colours
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Paints

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.
Ambersil House - Wylde Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom
Tel.: +44 1278 727200
Fax.: +44 1278 425644
E-mail : hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

| | |
|------------------------|--|
| Physical: | Aerosols, category 1 Extremely flammable aerosol. Pressurised container: May burst if heated. |
| Health: | Eye irritation, category 2 Causes serious eye irritation. Specific target organ toxicity - single exposure, category 3 May cause drowsiness or dizziness. |
| Environment: | Not classified |
| Other hazards : | Repeated exposure may cause skin dryness or cracking. |

Classification according to 67/548/EEC or 1999/45/EC:

| | |
|---|--|
| Productname : Acrylic Paint | Creationdate : 25.06.14 Version : 2.0 |
| Ref.Nr.: BDS000794_3_20140625 (EN) | Replaces: BDS000794_20120614 |

EXTREMELY FLAMMABLE



Xi : IRRITANT

Health: R36: Irritating to eyes.
R66: Repeated exposure may cause skin dryness or cracking.
R67: Vapours may cause drowsiness and dizziness.

Physical: EXTREMELY FLAMMABLE**Environment:** Not classified

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

| | |
|---|--|
| Product identifier: | Contains: acetone; propan-2-one; propanone n-butyl acetate |
| Hazard pictogram(s): |   |
| Signal word: | Danger |
| Hazard statement(s): | H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H319 : Causes serious eye irritation. H336 : May cause drowsiness or dizziness. |
| Precautionary statement(s): | P101 : If medical advice is needed, have product container or label at hand. P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P260 : Do not breathe dust/fume/gas/mist/vapours/spray. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point. |
| Supplemental Hazard information: | Repeated exposure may cause skin dryness or cracking. |

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

| Hazardous ingredient | CAS-nr. | EC-nr | w/w % | symbol | R-phrases* | Notes |
|----------------------|---------|-------|-------|--------|------------|-------|
|----------------------|---------|-------|-------|--------|------------|-------|

Productname : Acrylic Paint
Ref.Nr.: BDS000794_3_20140625 (EN)

Creationdate : 25.06.14 Version : 2.0
Replaces: BDS000794_20120614

| | | | | | | |
|---|------------|-----------|---------|------|----------------------|-----|
| acetone; propan-2-one; propanone | 67-64-1 | 200-662-2 | 25-50 | F,Xi | 11-36-66-67 | A |
| dimethyl ether | 115-10-6 | 204-065-8 | 12.5-20 | F+ | 12 | A |
| n-butyl acetate | 123-86-4 | 204-658-1 | 12.5-20 | | 10-66-67 | |
| butane (<= 0,1 % butadiene) | 106-97-8 | 203-448-7 | 5-10 | F+ | 12 | |
| 2-methoxy-1-methylethyl acetate | 108-65-6 | 203-603-9 | 5-10 | | 10 | A |
| isobutane (<= 0,1 % butadiene) | 75-28-5 | 200-857-2 | 2.5-5 | F+ | 12 | |
| Solvent naphtha (petroleum), light arom. (benzene<0.1%) | 64742-95-6 | 265-199-0 | 0-1 | Xn,N | 10-37-51/53-65-66-67 | B,P |
| propane | 74-98-6 | 200-827-9 | 10-12.5 | F+ | 12 | B |

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

P : not classified as carcinogen, less than 0.1% w/w benzene (Einecs-nr. 200-753-7)

| Hazardous ingredient | Registration number | CAS-nr. | EC-nr | w/w % | Hazard Class and Category | Hazard statement | Notes |
|---|---------------------|------------|-----------|---------|--|-------------------------------|-------|
| acetone; propan-2-one; propanone | 01-2119471330-49 | 67-64-1 | 200-662-2 | 25-50 | Flam. Liq. 2, Eye Irrit. 2, STOT SE 3 | H225,H319,H336 | A |
| dimethyl ether | 01-2119472128-37 | 115-10-6 | 204-065-8 | 12.5-20 | Flam. Gas 1, Press. Gas | H220,H280 | A |
| n-butyl acetate | 01-2119485493-29 | 123-86-4 | 204-658-1 | 12.5-20 | Flam. Liq. 3, STOT SE 3 | H226,H336 | |
| butane (<= 0,1 % butadiene) | 01-2119474691-32 | 106-97-8 | 203-448-7 | 5-10 | Flam. Gas 1, Press. Gas | H220 | |
| 2-methoxy-1-methylethyl acetate | 01-2110475791-29 | 108-65-6 | 203-603-9 | 5-10 | Flam. Liq. 3 | H226 | A |
| isobutane (<= 0,1 % butadiene) | 01-2119485395-27 | 75-28-5 | 200-857-2 | 2.5-5 | Flam. Gas 1, Press. Gas | H220 | |
| Solvent naphtha (petroleum), light arom. (benzene<0.1%) | | 64742-95-6 | 265-199-0 | 0-1 | Flam. Liq. 3, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2 | H226,H315,H335,H336,H304,H411 | B,P |
| propane | 01-2119486944-21 | 74-98-6 | 200-827-9 | 10-12.5 | Flam. Gas 1, Press. Gas | H220,H280 | B |

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

P : not classified as carcinogen, less than 0.1% w/w benzene (Einecs-nr. 200-753-7)

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

| | |
|----------------------------|---|
| Contact with eyes : | IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. |
| Contact with skin : | Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention. |
| Inhalation : | IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell. |
| Ingestion : | If swallowed accidentally, do not induce vomiting and seek medical advice. |

Productname : Acrylic Paint
Ref.Nr.: BDS000794_3_20140625 (EN)
Creationdate : 25.06.14 Version : 2.0
Replaces: BDS000794_20120614

4.2. Most important symptoms and effects, both acute and delayed

| | |
|-----------------------|---|
| Inhalation : | Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness |
| Ingestion : | May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting |
| Skin contact : | May cause irritation. Symptoms : redness and pain |
| Eye contact : | Irritating to eyes Symptoms : redness and pain |

4.3. Indication of any immediate medical attention and special treatment needed

| | |
|-------------------------|---|
| General Advice : | If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor |
|-------------------------|---|

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO₂

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Productname : Acrylic Paint
Ref.Nr.: BDS000794_3_20140625 (EN)
Creationdate : 25.06.14 Version : 2.0
Replaces: BDS000794_20120614

Absorb spillage in suitable inert material
 Place in appropriate container

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
 Take precautionary measures against static discharges
 Equipment should be earthed
 Use explosion-proof electrical/ventilating/lighting/.../equipment.
 Use only non-sparking tools.
 Do not breathe aerosols or vapours.
 Ensure adequate ventilation
 Avoid contact with skin and eyes.
 Wash thoroughly after use
 Wear protective gloves/protective clothing/eye protection/face protection.
 Eyewash bottles should be available

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
 Keep out of reach of children.

7.3. Specific end use(s)

Paints

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

| Hazardous ingredient | CAS-nr. | method | |
|---|----------|--------|----------|
| EU established exposure limits: | | | |
| 2-methoxy-1-methylethyl acetate | 108-65-6 | TWA | 50 ppm |
| | | STEL | 100 ppm |
| dimethyl ether | 115-10-6 | TWA | 1000 ppm |
| acetone; propan-2-one; propanone | 67-64-1 | TWA | 500 ppm |
| National established exposure limits, United Kingdom | | | |
| butane (<= 0,1 % butadiene) | 106-97-8 | TWA | 600 ppm |
| | | STEL | 750 ppm |

Productname : Acrylic Paint
Ref.Nr.: BDS000794_3_20140625 (EN)
Creationdate : 25.06.14 Version : 2.0
Replaces: BDS000794_20120614

| | | | |
|----------------------------------|----------|------|----------|
| dimethyl ether | 115-10-6 | TWA | 400 ppm |
| | | STEL | 500 ppm |
| n-butyl acetate | 123-86-4 | TWA | 150 ppm |
| | | STEL | 200 ppm |
| acetone; propan-2-one; propanone | 67-64-1 | TWA | 500 ppm |
| | | STEL | 1500 ppm |

8.2. Exposure controls

| | |
|----------------------------------|---|
| Control procedures : | Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges |
| Personal protection : | Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation |
| inhalation : | In case of insufficient ventilation, wear suitable respiratory equipment. (filter AXP2) |
| hands and skin : | Wear suitable protective gloves against chemicals (butyl rubber) |
| eyes : | Wear safety goggles. |
| Environmental protection: | Avoid release to the environment. Collect spillage. |

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

| | |
|---|----------------------------------|
| Apperance : physical state : | Liquid under pressure. |
| colour : | See color cap. |
| odour : | Characteristic odor. |
| pH : | Not applicable. |
| Boiling point/range : | Not available. |
| Flash point : | < 0 °C |
| Evaporation rate : | Not available. |
| Explosion limits : upper limit : | 18.6 % |
| lower limit : | 1.2 % |
| Vapour pressure : | 830 kPa (@ 20°C). |
| Relative density : | 0.87 g/cm ³ (@ 20°C). |
| Solubility in water : | Not available. |
| Auto-ignition : | > 200 °C |
| Viscosity : | Not applicable. |

9.2. Other information

VOC: 815 g/l

SECTION 10: Stability and reactivity

Productname : Acrylic Paint
Ref.Nr.: BDS000794_3_20140625 (EN)
Creationdate : 25.06.14 Version : 2.0
Replaces: BDS000794_20120614

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information**11.1. Information on toxicological effects**

Inhalation : Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion : May cause gastrointestinal disturbances
Skin contact : May cause irritation.
Eye contact : Irritating to eyes

Toxicological data :

| Hazardous ingredient | CAS-nr. | method | |
|----------------------------------|----------|-----------------|--------------|
| 2-methoxy-1-methylethyl acetate | 108-65-6 | LD50 oral rat | > 5000 mg/kg |
| | | LD50 derm.rabit | > 5000 mg/kg |
| n-butyl acetate | 123-86-4 | LD50 oral rat | > 2000 mg/kg |
| | | LC50 inhal.rat | > 20 mg/l |
| acetone; propan-2-one; propanone | 67-64-1 | LD50 oral rat | > 5000 mg/kg |
| | | LC50 inhal.rat | > 20 mg/l |
| | | LD50 derm.rabit | > 2000 mg/kg |

SECTION 12: Ecological information

Productname : Acrylic Paint
Ref.Nr.: BDS000794_3_20140625 (EN)

Creationdate : 25.06.14 Version : 2.0
Replaces: BDS000794_20120614

12.1. Toxicity

Not classified

Ecotoxicological data:

| Hazardous ingredient | CAS-nr. | method | |
|----------------------------------|----------|--------------|------------|
| 2-methoxy-1-methylethyl acetate | 108-65-6 | LC50 fish | > 100 mg/l |
| | | EC50 daphnia | > 400 mg/l |
| n-butyl acetate | 123-86-4 | IC50 algae | 647 mg/l |
| | | LC50 fish | 18 mg/l |
| acetone; propan-2-one; propanone | 67-64-1 | EC50 daphnia | 44 mg/l |
| | | IC50 algae | > 100 mg/l |
| | | LC50 fish | > 100 mg/l |
| | | EC50 daphnia | > 100 mg/l |

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

No experimental data available

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

National regulations : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

Productname : Acrylic Paint
Ref.Nr.: BDS000794_3_20140625 (EN)
Creationdate : 25.06.14 Version : 2.0
Replaces: BDS000794_20120614

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)

Class: 2.1

ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No

IMDG - Marine pollutant: No

IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)

IMDG - Ems: F-D, S-U

IATA/ICAO - PAX: 203

IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.
Regulation (EC) No 1272/2008 (CLP)
EU-directive 99/45/EC
Regulation (EC) No 1907/2006 (REACH)

15.2. Chemical safety assessment

No information available

Productname : Acrylic Paint
Ref.Nr.: BDS000794_3_20140625 (EN)

Creationdate : 25.06.14 Version : 2.0
Replaces: BDS000794_20120614

SECTION 16: Other information

*Explanation risk-phrases: R10: Flammable.
R11: Highly flammable.
R12: Extremely flammable.
R36: Irritating to eyes.
R37: Irritating to respiratory system.
R65: Harmful: may cause lung damage if swallowed.
R66: Repeated exposure may cause skin dryness or cracking.
R67: Vapours may cause drowsiness and dizziness.
R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

*Explanation hazard statements: H220 : Extremely flammable gas.
H225 : Highly flammable liquid and vapour.
H226 : Flammable liquid and vapour.
H280 : Contains gas under pressure; may explode if heated.
H304 : May be fatal if swallowed and enters airways.
H315 : Causes skin irritation.
H319 : Causes serious eye irritation.
H335 : May cause respiratory irritation.
H336 : May cause drowsiness or dizziness.
H411 : Toxic to aquatic life with long lasting effects.

REVISIONS IN CHAPTRE : 2.2. Label elements

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.