

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

10-11-2033

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 Crimp Housing, High Pressure, 3 Circuits



Series

image - Reference only

Documents:

- 3D Model

Packaging Specification PK-7880-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-7879 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

7880

Application

Signal, Wire-to-Board

Overview

KK® Interconnect System - Molex

Product Name

KK® 254

UPC

800753612280

Physical

Circuits (maximum)

3

Color - Resin

Natural (White)

Flammability

94V-0

Gender

Female

Glow-Wire Compliant

No

Material - Resin

Nylon

Net Weight

0.294/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

2.54mm

Pitch - Termination Interface

2.54mm

Stackable

No

Temperature Range - Operating

See Product Specification

Material Info

Old Part Number

7880-3B

Reference - Drawing Numbers

Packaging Specification

PK-7880-001

Product Specification

PS-7879

Sales Drawing

SD-7880

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

7880Series

Mates With

KK®254 PCB Headers [42375](#) , [42377](#) ,
[42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With

[7879](#) KK® High Pressure Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION