

160[®] Handi-VOM



Smallest and Handiest of Simpson's Shock Resistant Analog VOMs

The 160 combines the performance and reliability of the famouse Simpson 260 in a convenient hand-held package.

The self-shielding taut-band movement features outstanding repeatability and resistance to stray magnetic fields.

Internal circuits protect the meter from accidental overload.

- Ideal for Nulling, Peaking and Trend Information
- Quick, Positive "Yes/No" Checks for Voltage, Current and Continuity
- Does Not Generate RF Radiation Which can cause Interference or Trigger External Sensitive Circuits
- High Immunity to Voltage Transients and RF Interference-No Expensive Chips to Wipe Out
- Includes 22.5V and 1.5V Batteries and Test Leads With Probe Tip

Rev. 04-15



160[®] Handi-VOM

Ordering Information		
VOM	Catalog Number	
160, Compact	12271	
Accessories	Catalog Number	
Accessories Test Leads w/Probe Tip	Catalog Number 02055	

Specifications

DC Voltage		
Ranges	Accuracy	Sensitivity
250mV, 1V, 2.5V, 10V, 50V, 250V, 500V, 1000V	2% of full scale	20KΩ per volt

AC Voltage		
Ranges	Accuracy	Sensitivity
2.5V, 10V, 50V, 250V, 500V, 1000V	3% of full scale	5KΩ per volt

Decibel	
Ranges	-20 to +50dB
Reference	0dB = 1mW into 600Ω

DC Current		
Ranges	Accuracy	Voltage Drop: (Nominal)
50μA, 1mA, 10mA, 100mA, 250mA, 500mA	2% of full scale	350mV Maximum

Resistance		
Ranges	Accuracy	Maxium Indication
Rx1		0 - 3ΚΏ
Rx10		0 - 30ΚΩ
Rx100	3° of arc	0 - 300ΚΏ
Rx1K		0 - 3ΜΩ
Rx10K		0 - 30ΜΏ

Batteries	1.5V AA, 22.5V (Neda No.13F, Eveready 505)
Operating Temperature Range	75°F for rated accuracy; less than 4% additional error over the range of +25°F to +130°F
Size	4-9/16" x 3-5/16" x 1-3/4" (11.59 x 8.41 x 4.45 cm)
Weight	Approximately 12 ounces (.34 Kg)
Construction	Combination high impact plastic and phenolic case
Circuit To Ground Voltage	1000V AC/DC Max

Specifications subject to change without notice.

2 Rev. 04-15