




MPZ1608S331ATA00

Applications	 Commercial Grade
Feature	 Power Line
Series	MPZ Series / MPZ1608 Type
Status	Production




Size	
Length(L)	1.60mm +/-0.15mm
Width(W)	0.80mm +/-0.15mm
Thickness(T)	0.80mm +/-0.15mm
Recommended Land Pattern (A)	0.60mm Nom.
Recommended Land Pattern (B)	0.80mm Nom.
Recommended Land Pattern (C)	0.80mm Nom.

Electrical Characteristics	
Impedance at 100MHz	330Ω +/-25%
Rated Current	1.7A
DC Resistance [Max.]	80mΩ


Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000Pcs Min.
Weight	0.004g

MPZ1608S331ATA00



Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



MPZ1608S331ATA00(Z) MPZ1608S331ATA00(R) MPZ1608S331ATA00(X)



MPZ1608S331ATA00



MPZ1608S331ATA00

- This PDF document was created based on the data listed on the TDK Corporation website.
- All specifications are subject to change without notice.