



GU10

Cat # CGGU25B4D

Performance Parameters	Units	Value			Test Condition Notes
		Min	Spec	Max	
Supply Voltage AC	V	120			
Input Power	W		7W±10%		
Luminous Flux	3000K lm	500	–	–	
Color Temperature	K	2870	3045	3220	
Color Rendering Index (CRI)	Ra	>80			
Beam Angle	°	35°			
Energy Star Certified		Yes			
Dimming		Yes			
Base Type		GU10			
Input Frequency	Hz	60 Hz			
Input Current	mA	–	60	–	
Power Factor	λ	≥0.9			
Dimming Range		10–100%			25°C
Luminous Efficiency	3000K lm/W	77	–	–	
Color Temperature	K	2870	3045	3220	

Starting and Lifetime		Min	Spec	Max	Test Condition Notes
L ₇₀ Life Time	hrs	–	25000	–	25°C
Start Up Time Without Dimmer	S	–	–	1	Rated Supply Voltage 25°C
Operating Temperature Range	°C	-20	25	45	

Safety Characteristics

Certification: UL, FCC, RoHS

Standard: UL1993, UL8750, Part15

Damp locations only. Do not use where directly exposed to water. Not for use in totally enclosed luminaires.

GU10

Cat # CGGU25B4D



Catalog #	CGGU25B4D
Description	GU10 3000K, 35°, Dimmable
Stock Number	70-0800-3030-0
Billing Unit	EA
Qty/Case	8
MOQ	1 Case
Item UPC	000-51128-94421-9
Case UPC	500-51128-94421-4
Case Dimension L × W × H	9.915" × 5.505" × 5.5"
Case Weight (lbs)	1.999
Case Cube (cu. ft.)	0.174

LIMITED WARRANTY: Warranted to last 3 years based on 3 hours normal use per day at 120 V. 3M makes no other warranties, express or implied, including any warranty of merchantability or fitness for a particular purpose. At 3M's option, refund or replacement is the sole remedy. This Limited Warranty does not cover accident, neglect, abuse, misuse or acts of God. LIABILITY FOR DIRECT, INDIRECT, INCIDENTAL OR CONSEQUENTIAL DAMAGES IS EXPRESSLY EXCLUDED, except where prohibited by law. For warranty claims and additional details, please visit 3MLighting.com/LED.

3M

3M Company
3M Center
St. Paul, MN 55144-1000
1.800.430.5000
3MLighting.com/LED

3M is a trademark of 3M. Used under license in Canada. All other trademarks herein are property of their respective owners. Please recycle.
Printed in USA. ©3M 2014. All rights reserved.
HB10116 11012014 98-0004-1012-0