

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

09-50-8053

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 3.96mm Crimp Terminal Housing, Friction Ramp, 5 Circuits



image - Reference only

Series

- Documents:
- 3D Model

Packaging Specification PK-41695-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-08-50 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

41695

Application

Power, Wire-to-Board

MolexKits

Yes

Overview

KK® Interconnect System - Molex

Product Name

KK® 396

UPC

800754227728

Physical

Breakaway

No

Circuits (maximum)

5

Color - Resin

Natural

Flammability

94V-0

Gender

Female

Glow-Wire Compliant

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Resin

Polyester

Net Weight

1.788/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

3.96mm

Polarized to Mating Part

Yes

Temperature Range - Operating

See Product Specification

Material Info

Old Part Number

41695-N-D05

Reference - Drawing Numbers

Packaging Specification

PK-41695-001

Product Specification

PS-08-50

Sales Drawing

SD-41695

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
41695Series

Mates With
KK® 396 Header [41791](#) , [41792](#) , [41671](#) ,
[41672](#) , [41661](#) , [41662](#)

Use With
KK® 396 Crimp Terminals, [2478](#) , [2578](#) ,
[6838](#) , [7258](#) , [45570](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION