





(1,27 mm) .050"

TIGER EYE" DISCRETE CABLE ASSEMBLY

SPECIFICATIONS

For complete specifications see www.samtec.com?SFSS, www.samtec.com?SFSD, www.samtec.com?SFSDT or www.samtec.com?SFSST

Insulator Material: Black LCP Contact Material: BeCu Plating:

Au over 50μ" (1,27 μm) Ni Current Rating (SFSD/TFC): 2.9 A per pin (1 pin powered per row) Operating Temp Range: -10°C to +80°C (PVC) -40°C to +125°C (*Teflon®) Voltage Rating: 275 VAC (PVC) 235 VAC (*Teflon® Wire: 28 or 30 AWG RoHS Compliant: Yes

*DuPont™ Teflon® is a registered trademark of the du Pont de Nemours and Company or its affiliates.

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



APPLICATION

-28C CABLE COLOR CODING	
PIN	COLOR
1	BROWN
2	RED
3	ORANGE
4	YELLOW
5	GREEN
6	VIOLET
7	GRAY
8	WHITE
9	BLACK
10	BLUE
ETC	REPEAT

ALSO AVAILABLE (MOQ Required)

- Other sizes
- · Locking feature for mating to the TFML Series
- · Color coded cable (*Teflon® N/A)
- · Other plating options Contact Samtec.

For wiring option and pin position location information. refer to drawings on web.

Some lengths, styles and options are non-standard, non-returnable.



FM, TFC (-SR & -DR requires -WT option)

Min


Max

Avg

Min

Max

Avg



TYPE STRIP

SFSS

= Single

Row

PVC Cable

SFSST

= Single

Row

*Teflon®

Cable

SFSD

= Double

Row

PVC Cable

SFSDT

= Double

Row

*Teflon®

Cable

(1.65) .065 -

(2,86) 1.113

POSITIONS PER ROW

(29,95 N) 6.73 lb

-04·05, –07 ·10. –15.

20, –25 -40<u>, –50</u> (Standard sizes)


WIRE GAUGE

-30 = 30 AWG -28 ·28C

= 28 AWG = Color Coded Cable (SFSS, SFSD only **PLATING OPTION**

-G = 10µ" (0,25 µm) Gold on contact, Gold Flash on balance

No. of Positions x (1,27) .050 + (0,38) .015 End 1 Notch



-D-NUS

ASSEMBLED LENGTH

"XX.XX

= Assembled Length in Inches (76,20 mm) 03.00" min. for –S end option (82,60 mm) 03.25" min. for -D end option

For –(X) specify "S" for single ended and "D" for double ended.

-(X)R = Retention Latch (TFM -WT option required for mating)

END

OPTION

= Single Ended

–D

= Double Ended

(X)S = Screw Down (Not available in -50 positions (Not available with SFSS, SFSST) (Mates with TFM-DS option)

Teflon® cable is intended for

solderable cable applicators.

crimp only. Contact Samtec for

0

Note:

SFSS

END 2 **OPTION**

Requires -D, -DS or -DR (End 1 Notch Up)

-NUS = Notch up, straight (Pin 1 to Pin N-1)

-NDS Notch down, straight (Pin 1 to Pin 2)

-NUX = Notch up, crossed (Pin 1 to Pin N) (SFSD/ SFSDT only)

–NDX Notch down, crossed

(Pin 1 to Pin 1) (SFSD/ SFSDT only)

SFSD